

# UMK- 4 RM 24 - Multiple relay module



2971344

<https://www.phoenixcontact.com/us/products/2971344>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, for 4 plug-in miniature relays or miniature optocouplers, with LED, 24 V AC/DC input voltage

## Commercial data

Item number	2971344
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK6164
GTIN	4017918088330
Weight per piece (including packing)	152.6 g
Weight per piece (excluding packing)	111.76 g
Customs tariff number	85364190
Country of origin	DE

# UMK- 4 RM 24 - Multiple relay module



2971344

<https://www.phoenixcontact.com/us/products/2971344>

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Multi-channel relay module
No. of channels	4
Compatible components	Miniature relays or miniature optocouplers
With components	no

#### Insulation characteristics

Overvoltage category	III
Pollution degree	2

### Electrical properties

Rated insulation voltage	260 V AC
Rated surge voltage	4 kV (Basic insulation between output contact current paths) 6 kV (Safe isolation and reinforced insulation between input circuit and output contact paths)

### Input data

Nominal input voltage $U_N$	24 V AC/DC $\pm 10\%$
Input voltage range in reference to $U_N$	0.8 ... 1.1
Typical input current at $U_N$	2 mA
Protective circuit	Bridge rectifier; Bridge rectifier
Status display/channel	Yellow LED

### Output data

Compatible components	Miniature relays or miniature optocouplers
-----------------------	--

#### Switching

Contact switching type	1 changeover contact
Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	8 A
Error detection (line break / short-circuit)	no

### Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of connections	1

# UMK- 4 RM 24 - Multiple relay module



2971344

<https://www.phoenixcontact.com/us/products/2971344>

Number of positions	6
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of connections	12
Number of positions	3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Dimensions

Width	67.5 mm
Height	77 mm
Depth	59 mm

## Material specifications

Color	green (RAL 6021)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	DIN EN 50178
	IEC 60664

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any


# UMK- 4 RM 24 - Multiple relay module

2971344

<https://www.phoenixcontact.com/us/products/2971344>

## Drawings

Circuit diagram



# UMK- 4 RM 24 - Multiple relay module

2971344

<https://www.phoenixcontact.com/us/products/2971344>



## Classifications

### UNSPSC

UNSPSC 21.0	39122335
-------------	----------

# UMK- 4 RM 24 - Multiple relay module



2971344

<https://www.phoenixcontact.com/us/products/2971344>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)