

USBR 2-11 - Bridge bar

3001356

<https://www.phoenixcontact.com/us/products/3001356>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge bar, number of positions: 2, color: silver-colored



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3001356 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE19 |
| Product key | BE1Z3X |
| GTIN | 4046356857284 |
| Weight per piece (including packing) | 7.26 g |
| Weight per piece (excluding packing) | 7.2 g |
| Customs tariff number | 85369095 |
| Country of origin | IN |

USBR 2-11 - Bridge bar



3001356

<https://www.phoenixcontact.com/us/products/3001356>

Technical data

Product properties

| | |
|---------------------|------------|
| Product type | Bridge bar |
| Number of positions | 2 |
| Potentials | 2 |

Material specifications

| | |
|-------|----------------|
| Color | silver-colored |
|-------|----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

USBR 2-11 - Bridge bar

3001356

<https://www.phoenixcontact.com/us/products/3001356>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000489 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

USBR 2-11 - Bridge bar



3001356

<https://www.phoenixcontact.com/us/products/3001356>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 4da2a354-5bc5-4fb1-b109-ae8347569566 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com