

APH-ME - Cover profile carrier




3034374

<https://www.phoenixcontact.com/us/products/3034374>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover profile carrier, for mounting on NS 35/7,5 DIN rail, for fixing the AP-ME cover profile, including mounting screws and plastic knurled nuts, can be sealed as an option



Your advantages

- It offers parking options for FBS ...-8 plug-in bridges and can be sealed as an option
- The APH-ME end bracket is used in conjunction with the AP-ME cover

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3034374 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE06 |
| Product key | BE61ZX |
| GTIN | 4046356316767 |
| Weight per piece (including packing) | 28.17 g |
| Weight per piece (excluding packing) | 27.28 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

APH-ME - Cover profile carrier

3034374


<https://www.phoenixcontact.com/us/products/3034374>

Technical data

Product properties

| | |
|--------------|-----------------------|
| Product type | Cover profile carrier |
|--------------|-----------------------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 8.2 mm |
| Height | 138 mm |
| Depth | 91.8 mm |
| Depth on NS 35/7,5 | 92.5 mm |
| Length | 138 mm |

Material specifications

| | |
|---|-----------------|
| Color | gray (RAL 7042) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

APH-ME - Cover profile carrier

3034374

<https://www.phoenixcontact.com/us/products/3034374>



Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |


APH-ME - Cover profile carrier

3034374

<https://www.phoenixcontact.com/us/products/3034374>



Drawings



APH-ME - Cover profile carrier



3034374

<https://www.phoenixcontact.com/us/products/3034374>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250302 |
| ECLASS-15.0 | 27250302 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001041 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

APH-ME - Cover profile carrier



3034374

<https://www.phoenixcontact.com/us/products/3034374>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.169 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com