

ZTRK 4 OG - Transformer terminal block




3029305

<https://www.phoenixcontact.com/us/products/3029305>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spring-cage transformer terminal block, with solder connection, color: orange



Commercial data

Item number	3029305
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	AA18
Product key	AARABE
GTIN	4017918193263
Weight per piece (including packing)	5.52 g
Weight per piece (excluding packing)	5.468 g
Customs tariff number	85369010
Country of origin	PL

ZTRK 4 OG - Transformer terminal block

3029305

<https://www.phoenixcontact.com/us/products/3029305>

Technical data

Product properties

Product type	Distributor terminal block
Number of positions	4
Number of connections	2

Insulation characteristics

Overvoltage category	III
Degree of pollution	3


Electrical properties

Maximum load current	32 A (with 4 mm ² conductor cross-section)
Rated surge voltage	6 kV

Connection data

Maximum load current	32 A (with 4 mm ² conductor cross-section)
Connection method	Spring-cage connection
Stripping length	12 mm
	12 mm
Internal cylindrical gage	A4
Connection in acc. with standard	IEC / EN
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Cross section AWG	24 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 4 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 4 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1 mm ²
Nominal current	32 A
Maximum load current	32 A
Nominal voltage	600 V

Dimensions

Dimensional drawing	
Width	7.5 mm
Height	39.8 mm
Length	32.6 mm

Material specifications

ZTRK 4 OG - Transformer terminal block



3029305

<https://www.phoenixcontact.com/us/products/3029305>

Color (Housing)	orange (RAL 2003)
Flammability rating according to UL 94	V0
Insulating material group	III
Insulating material	PA
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C

Electrical tests

Surge voltage test

Test voltage setpoint	6 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 4 mm ²	0.48 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	1.89 kV
Result	Test passed

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	TRS-AL 2/10 resp. TRS-AL 2/35
Test force setpoint	1 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	0.2 mm ² / 0.2 kg
	4 mm ² / 0.9 kg
Result	Test passed

Environmental and real-life conditions

Aging

Temperature cycles	192
Result	Test passed

Needle-flame test

ZTRK 4 OG - Transformer terminal block



3029305

<https://www.phoenixcontact.com/us/products/3029305>

Time of exposure	30 s
Result	Test passed

Standards and regulations

Connection in acc. with standard	IEC / EN
----------------------------------	----------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

ZTRK 4 OG - Transformer terminal block


3029305

<https://www.phoenixcontact.com/us/products/3029305>



Drawings

Dimensional drawing



ZTRK 4 OG - Transformer terminal block



3029305

<https://www.phoenixcontact.com/us/products/3029305>

Classifications

ECLASS

ECLASS-13.0	27141110
ECLASS-15.0	27141110

UNSPSC

UNSPSC 21.0	39121410
-------------	----------

ZTRK 4 OG - Transformer terminal block



3029305

<https://www.phoenixcontact.com/us/products/3029305>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com