

# P-FU 5X20-EX - Fuse plug

3036807

<https://www.phoenixcontact.com/us/products/3036807>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse plug, nom. voltage: 500 V, nominal current: 6.3 A, connection method: Plug-in connection, fuse type: G / 5 x 20, color: black

## Your advantages

- Large-surface labeling option
- Test contacts on both sides of the fuse
- Versions with bipolar error display
- Can be used for overload/short-circuit protection

## Commercial data

Item number	3036807
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4046356919210
Weight per piece (including packing)	4.2 g
Weight per piece (excluding packing)	3.8 g
Customs tariff number	85369095
Country of origin	PL

# P-FU 5X20-EX - Fuse plug



3036807

<https://www.phoenixcontact.com/us/products/3036807>

## Technical data

### Notes

Notes on operation	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
--------------------	---

### Product properties

Product type	Fuse
Potentials	1

### Insulation characteristics

Degree of pollution	3
---------------------	---

### Electrical properties

Fuse	G / 5 x 20
------	------------

### Connection data

Connection method	Plug-in connection
Nominal current	6.3 A (the current is determined by the fuse used)
Maximum load current	6.3 A (the current is determined by the fuse used)
Nominal voltage	500 V (The voltage is determined by the fuse or selected LED display)

### Dimensions

Width	6.2 mm
Height	28 mm
Depth	25 mm
Length	28 mm

### Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

### Environmental and real-life conditions

#### Ambient conditions

# P-FU 5X20-EX - Fuse plug



3036807

<https://www.phoenixcontact.com/us/products/3036807>

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

# P-FU 5X20-EX - Fuse plug

3036807

<https://www.phoenixcontact.com/us/products/3036807>



## Drawings

### Application drawing



Fuse terminal blocks in interconnected arrangement,  
block consisting of 5 fuse terminal blocks

# P-FU 5X20-EX - Fuse plug

3036807

<https://www.phoenixcontact.com/us/products/3036807>



Application drawing



Fuse terminal block in single arrangement,  
block consisting of one fuse terminal block and 4 feed-through terminal blocks

# P-FU 5X20-EX - Fuse plug





3036807

<https://www.phoenixcontact.com/us/products/3036807>


## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3036807>


 <b>CSA</b> Approval ID: 158887				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	300 V	10 A	-	-

 <b>IECEE CB Scheme</b> Approval ID: NL-61580				
---	--	--	--	--


 <b>EAC</b> Approval ID: RU C-DE.BL08.B.00714				
---	--	--	--	--

 <b>cULus Recognized</b> Approval ID: E60425				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	300 V	10 A	-	-


 <b>cUL Recognized</b> Approval ID: E192998				
---	--	--	--	--

 <b>EAC Ex</b> Approval ID: RU C-DE.Ax07.B.03227				
--	--	--	--	--

 <b>UL Recognized</b> Approval ID: E192998				
--	--	--	--	--

 <b>CCC</b> Approval ID: 2020322313000632				
---	--	--	--	--

 <b>UKCA-EX</b> Approval ID: UL22UKEX2452U				
--	--	--	--	--

 <b>EAC Ex</b>				
---	--	--	--	--

# P-FU 5X20-EX - Fuse plug

3036807

<https://www.phoenixcontact.com/us/products/3036807>



Approval ID: KZ 7500525010101950

# P-FU 5X20-EX - Fuse plug

3036807

<https://www.phoenixcontact.com/us/products/3036807>



## Classifications

### ECLASS

ECLASS-13.0	27250305
ECLASS-15.0	27250305

### ETIM

ETIM 10.0	EC002018
-----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# P-FU 5X20-EX - Fuse plug



3036807

<https://www.phoenixcontact.com/us/products/3036807>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)