

PS-6/2,3MM RD - Test plug



3038736

<https://www.phoenixcontact.com/us/products/3038736>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, number of positions: 1, color: red

Your advantages

- Housing for test plugs, any combination
- The test plugs are inserted in the function shaft of the terminal blocks from the CLIPLINE complete system or in the test pick-offs provided

Commercial data

Item number	3038736
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4017918904166
Weight per piece (including packing)	1.43 g
Weight per piece (excluding packing)	1.18 g
Customs tariff number	85366990
Country of origin	DE

PS-6/2,3MM RD - Test plug



3038736

<https://www.phoenixcontact.com/us/products/3038736>

Technical data

Product properties

Product type	Test plug terminal block
Number of positions	1
Pitch	6 mm

Connection data

Connection method	Spring-cage connection
-------------------	------------------------

Dimensions

Width	6.2 mm
Height	14 mm
Depth on NS 35/7,5	36 mm
Pitch	6 mm

Material specifications

Color	red (RAL 3001)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ()
Permissible humidity (storage/transport)	30 % ... 70 %

PS-6/2,3MM RD - Test plug



3038736

<https://www.phoenixcontact.com/us/products/3038736>

Classifications

ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

ETIM

ETIM 10.0	EC002555
-----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PS-6/2,3MM RD - Test plug



3038736

<https://www.phoenixcontact.com/us/products/3038736>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.062 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com