

STN 35 - N disconnect terminal block

3038299

<https://www.phoenixcontact.com/us/products/3038299>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



N disconnect terminal block, **Assembly instructions:**

For secure fastening of the neutral busbar, supports must be set at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips., nom. voltage: 400 V, nominal current: 125 A, Spring-cage connection, 1st level connection right, Rated cross section: 35 mm², cross section: 2.5 mm² - 35 mm², mounting type: NS 35/15, NS 35/7,5, color: blue

Commercial data

Item number	3038299
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE02
Product key	BE2152
GTIN	4017918899790
Weight per piece (including packing)	86.6 g
Weight per piece (excluding packing)	81.1 g
Customs tariff number	85369010
Country of origin	RO

STN 35 - N disconnect terminal block



3038299

<https://www.phoenixcontact.com/us/products/3038299>

Technical data

Notes

General	Assembly instructions: For secure fastening of the neutral busbar, supports must be set at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips.
---------	---

Product properties

Product type	Installation terminal block
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
---------------------	------

Connection data

Number of connections per level	2
Nominal cross section	35 mm ²
Tightening torque disconnect slide	M5 2.5 ... 3 Nm

1st level connection right

Connection method	Spring-cage connection
Stripping length	25 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	2.5 mm ² ... 35 mm ²
Cross section AWG	14 ... 2 (converted acc. to IEC)
Conductor cross-section flexible	2.5 mm ² ... 35 mm ²
Conductor cross-section, flexible [AWG]	14 ... 2 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	2.5 mm ² ... 35 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	2.5 mm ² ... 35 mm ²
Nominal cross section	35 mm ²
Nominal current	125 A
Maximum load current	125 A (with 35 mm ² conductor cross-section)
Nominal voltage	400 V

Dimensions

Width	16 mm
-------	-------

Material specifications

STN 35 - N disconnect terminal block



3038299

<https://www.phoenixcontact.com/us/products/3038299>

Color	blue
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/15
	NS 35/7,5
Screw thread	M5

STN 35 - N disconnect terminal block

3038299

<https://www.phoenixcontact.com/us/products/3038299>



Drawings

Circuit diagram



STN 35 - N disconnect terminal block



3038299

<https://www.phoenixcontact.com/us/products/3038299>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com