

UK 10,3-HESILED N 72 2POL - Fuse modular terminal block



3048674

<https://www.phoenixcontact.com/us/products/3048674>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a version of the article

Fuse modular terminal block, fuse type: Glass, fuse type: Midget / 10.3 x 38, nom. voltage: 690 V, nominal current: 32 A, connection method: Screw connection, Rated cross section: 16 mm², cross section: 1.5 mm²- 25 mm², mounting type: NS 35/7,5, NS 35/15, color: black

Your advantages

- For 10 x 38 fuse-links in accordance with IEC 60269-2
- 2-pos. blocked version
- Fuse holder for 12 V ... 72 V AC/DC fuses
- Quick identification of faulty fuses regardless of the current direction, thanks to LED status indicator
- Easy to bridge

Commercial data

Item number	3048674
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BE12
Product key	BE1234
GTIN	4046356504034
Weight per piece (including packing)	99.99 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	85369095
Country of origin	DE

UK 10,3-HESILED N 72 2POL - Fuse modular terminal block



3048674

<https://www.phoenixcontact.com/us/products/3048674>

Technical data

Product properties

Product type	Fuse terminal block
Number of connections	2
Number of rows	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Fuse type	Glass
Rated surge voltage	6 kV
Fuse	Midget / 10.3 x 38

Connection data

Nominal cross section	16 mm ²
-----------------------	--------------------

Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M5
Tightening torque	2.5 ... 3 Nm
Stripping length	12 mm
Internal cylindrical gage	A7
Connection in acc. with standard	IEC 60947-1 / -3
Conductor cross-section rigid	1.5 mm ² ... 25 mm ²
Cross section AWG	16 ... 4 (converted acc. to IEC)
Conductor cross-section flexible	1.5 mm ² ... 16 mm ²
Conductor cross-section, flexible [AWG]	16 ... 6 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	1.5 mm ² ... 16 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	1.5 mm ² ... 16 mm ²
Cross-section with insertion bridge, rigid	10 mm ²
Cross-section with insertion bridge, flexible	10 mm ²
2 conductors with same cross section, rigid	1.5 mm ² ... 4 mm ²
2 conductors with same cross section, flexible	1.5 mm ² ... 4 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	1.5 mm ² ... 4 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm ² ... 10 mm ²
Nominal cross section	16 mm ²
Nominal current	32 A (the current and voltage are determined by the fuse)
Maximum load current	32 A (the current and voltage are determined by the fuse)
Nominal voltage	690 V (the current and voltage are determined by the fuse)

UK 10,3-HESILED N 72 2POL - Fuse modular terminal block



3048674

<https://www.phoenixcontact.com/us/products/3048674>

Dimensions

Width	18 mm
-------	-------

Material specifications

Color	black
Flammability rating according to UL 94	V0
Insulating material group	III a
Insulating material	PA

Standards and regulations

Connection in acc. with standard	IEC 60947-1 / -3
----------------------------------	------------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15

UK 10,3-HESILED N 72 2POL - Fuse modular terminal block




3048674

<https://www.phoenixcontact.com/us/products/3048674>

Drawings

Circuit diagram



UK 10,3-HESILED N 72 2POL - Fuse modular terminal block



3048674

<https://www.phoenixcontact.com/us/products/3048674>

Classifications

ECLASS

ECLASS-13.0	27250113
-------------	----------

UK 10,3-HESILED N 72 2POL - Fuse modular terminal block



3048674

<https://www.phoenixcontact.com/us/products/3048674>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com