

RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block with bolt connection method, cross section: 0.1 - 6 mm², AWG: 26 - 10, width 9 mm, color: gray

Your advantages

- Large-surface, consistent external and center labeling
- Mounting on standard DIN rails or directly in control boxes
- Compact screw connection of ring and fork-type cable lugs
- Cover profile that can be snapped directly onto the terminal blocks provides touch-proof protection
- Screw nuts and current bars are latched in the insulating housing and cannot be removed
- Bridge shaft for potential distribution using standard screw bridges
- The isolator bridge bar supports switchable cross connections; the bridge screw therefore has the function of a live contact

Commercial data

Item number	3059171
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE15
Product key	BE1515
GTIN	4046356534796
Weight per piece (including packing)	90.7 g
Weight per piece (excluding packing)	90.3 g
Customs tariff number	85369010
Country of origin	IN

RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

Technical data

Product properties

Product type	Bolt connection terminal block
Pitch	9 mm
Number of connections	8
Number of rows	1
Potentials	4

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.02 W

Connection data

Number of connections per level	8
Nominal cross section	4 mm ²

1 level

Connection method	Bolt connection
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal cross section	4 mm ²
Nominal current	32 A
Maximum load current	32 A
Nominal voltage	800 V

Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	0.1 mm ² ... 6 mm ²
Cross section range AWG	26 ... 10 (converted acc. to IEC)
Hole diameter	4.3 mm
Width	8 mm
Bolt diameter	4 mm
Screw thread	M4
Tightening torque	1.2 ... 1.4 Nm
Connection in acc. with standard	DIN 46237:1970-07
Cross section	0.5 mm ² ... 2.5 mm ²
Cross section range AWG	26 ... 10 (converted acc. to IEC)
Hole diameter	4.3 mm
Width	8 mm

RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

Bolt diameter	4 mm
Screw thread	M4
Tightening torque	1.2 ... 1.4 Nm
Identification color of ring cable lugs : red	1 mm ²
Identification color of ring cable lugs : blue	2.5 mm ²

Dimensions

Width	53.8 mm
Height	37 mm
Pitch	9 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

Mounting

Mounting type
direct screw connection

RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

Drawings

Circuit diagram



RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com