

# RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block with bolt connection method, cross section: 0.1 - 6 mm<sup>2</sup>, AWG: 26 - 10, width 9 mm, color: gray

## Your advantages

- Large-surface, consistent external and center labeling
- Mounting on standard DIN rails or directly in control boxes
- Compact screw connection of ring and fork-type cable lugs
- Cover profile that can be snapped directly onto the terminal blocks provides touch-proof protection
- Screw nuts and current bars are latched in the insulating housing and cannot be removed
- Bridge shaft for potential distribution using standard screw bridges
- The isolator bridge bar supports switchable cross connections; the bridge screw therefore has the function of a live contact

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 3059171                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BE15                           |
| Product key                          | BE1515                         |
| GTIN                                 | 4046356534796                  |
| Weight per piece (including packing) | 90.7 g                         |
| Weight per piece (excluding packing) | 90.3 g                         |
| Customs tariff number                | 85369010                       |
| Country of origin                    | IN                             |

# RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

## Technical data

### Product properties

|                       |                                |
|-----------------------|--------------------------------|
| Product type          | Bolt connection terminal block |
| Pitch                 | 9 mm                           |
| Number of connections | 8                              |
| Number of rows        | 1                              |
| Potentials            | 4                              |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 1.02 W |

### Connection data

|                                 |                   |
|---------------------------------|-------------------|
| Number of connections per level | 8                 |
| Nominal cross section           | 4 mm <sup>2</sup> |

#### 1 level

|                                  |   |
|----------------------------------|---|
| Connection method                | Bolt connection   |
| Stripping length                 | The stripping length depends on the specification provided by the cable lug manufacturer. |
| Connection in acc. with standard | IEC 60947-7-1   |
| Nominal cross section            | 4 mm <sup>2</sup>   |
| Nominal current                  | 32 A  |
| Maximum load current             | 32 A  |
| Nominal voltage                  | 800 V   |

#### Cable lug connection DIN 46234:1980-03

|                                  |   |
|----------------------------------|---|
| Connection in acc. with standard | DIN 46234:1980-03                           |
| Cross section                    | 0.1 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Cross section range AWG          | 26 ... 10 (converted acc. to IEC)           |
| Hole diameter                    | 4.3 mm                                      |
| Width                            | 8 mm  |
| Bolt diameter                    | 4 mm  |
| Screw thread                     | M4  |
| Tightening torque                | 1.2 ... 1.4 Nm                              |
| Connection in acc. with standard | DIN 46237:1970-07                           |
| Cross section                    | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Cross section range AWG          | 26 ... 10 (converted acc. to IEC)           |
| Hole diameter                    | 4.3 mm                                      |
| Width                            | 8 mm  |

# RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

|  |                     |
|--|---------------------|
| Bolt diameter                                  | 4 mm                |
| Screw thread                                   | M4                  |
| Tightening torque                              | 1.2 ... 1.4 Nm      |
| Identification color of ring cable lugs : red  | 1 mm <sup>2</sup>   |
| Identification color of ring cable lugs : blue | 2.5 mm <sup>2</sup> |

## Dimensions

|        |         |
|--------|---------|
| Width  | 53.8 mm |
| Height | 37 mm   |
| Pitch  | 9 mm    |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group   | I               |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|  |   |
|--|---|
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

# RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

## Mounting

| Mounting type           |
|-------------------------|
| direct screw connection |

# RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

## Drawings

### Circuit diagram



# RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# RSC 4-F/4 - Bolt connection terminal block



3059171

<https://www.phoenixcontact.com/us/products/3059171>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)