

# KDT-ST 9 - Filler plug

3063989

<https://www.phoenixcontact.com/us/products/3063989>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Filler plug, material: PA, length: 20 mm, diameter: 9 mm



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3063989       |
| Packing unit                         | 25 pc         |
| Minimum order quantity               | 25 pc         |
| Sales key                            | BF67          |
| Product key                          | AF7CZX        |
| GTIN                                 | 4046356301442 |
| Weight per piece (including packing) | 1.4 g         |
| Weight per piece (excluding packing) | 1.34 g        |
| Customs tariff number                | 39174000      |
| Country of origin                    | DE            |

# KDT-ST 9 - Filler plug

3063989

<https://www.phoenixcontact.com/us/products/3063989>

## Technical data


### Notes

|         |   |
|---------|---|
| General | The filler plugs are used to seal unused cable sleeves. |
|---------|---|

### Product properties

|              |               |
|--------------|---------------|
| Product type | Sealing plugs |
|--------------|---------------|

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Length              | 20 mm  |
| Diameter            | 9 mm   |

### Material specifications

|          |                  |
|----------|------------------|
| Color    | black (RAL 9005) |
| Material | PA               |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |  |
|---------------------------------|--|
| Degree of protection            | IP54 (Observe the assembly instructions) |
| Ambient temperature (operation) | -20 °C ... 80 °C                         |

### Mounting

|               |  |
|---------------|--|
| Assembly note | IP54: for vertical sealing frame mounting/for horizontal sealing frame mounting (downward cable outlet direction). |
|---------------|--|

# KDT-ST 9 - Filler plug



3063989

<https://www.phoenixcontact.com/us/products/3063989>



## Drawings

Dimensional drawing



Dimensional drawing

# KDT-ST 9 - Filler plug

3063989

<https://www.phoenixcontact.com/us/products/3063989>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 23111190 |
| ECLASS-15.0 | 27144492 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002610 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

# KDT-ST 9 - Filler plug



3063989

<https://www.phoenixcontact.com/us/products/3063989>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.024 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)