

# FTPR-3/15S - Test plug



3069972

<https://www.phoenixcontact.com/us/products/3069972>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Test plug, With twist grip, number of positions: 15, color: gray



The figure shows the 14-pos. version

## Your advantages

- Easy and time saving, thanks to functional grouping of switching operations
- Cost-effective, thanks to the tailored, modular design and use of standardized CLIPLINE complete accessories
- Space saving, thanks to offset test socket arrangement
- Safe, thanks to guided operation with patented twist grip
- The automatically generated transformer short circuit and the shock-proof design ensure the highest degree of safety during measurement
- Maximum safety with leading and automatic transformer short circuit
- The integrated, robust switch contact is designed for the most stringent demands, and the use of high-quality materials ensures the transmission of signal currents, even after multiple actuations

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3069972       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BE06          |
| Product key                          | BE6113        |
| GTIN                                 | 4055626395760 |
| Weight per piece (including packing) | 736.6 g       |
| Weight per piece (excluding packing) | 734 g         |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

# FTPR-3/15S - Test plug

3069972


<https://www.phoenixcontact.com/us/products/3069972>

## Technical data

### Product properties

|                     |                          |
|---------------------|--------------------------|
| Product type        | Test plug terminal block |
| Product family      | FAME 3                   |
| Number of positions | 15                       |
| Pitch               | 8.2 mm                   |
| Potentials          | 15                       |

### Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 154.9 mm                                                                           |
| Height              | 86 mm                                                                              |
| Pitch               | 8.2 mm                                                                             |

### Material specifications

|                                        |                 |
|----------------------------------------|-----------------|
| Color                                  | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0              |
| Insulating material                    | PA              |

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

# FTPR-3/15S - Test plug




3069972


<https://www.phoenixcontact.com/us/products/3069972>

## Drawings

Dimensional drawing



Circuit diagram



# FTPR-3/15S - Test plug



3069972

<https://www.phoenixcontact.com/us/products/3069972>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3069972>

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                | 300 V                 | 31 A                  | -                 | -                           |
| C                                                                                                                                | 300 V                 | 31 A                  | -                 | -                           |
| F                                                                                                                                | 690 V                 | 31 A                  | -                 | -                           |
| D                                                                                                                                | 600 V                 | 5 A                   | -                 | -                           |

|  <b>CSA</b><br>Approval ID: 13631 |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                      | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                    | 300 V                 | 31 A                  | -                 | -                           |
| C                                                                                                                    | 300 V                 | 31 A                  | -                 | -                           |
| D                                                                                                                    | 600 V                 | 5 A                   | -                 | -                           |

# FTPR-3/15S - Test plug



3069972

<https://www.phoenixcontact.com/us/products/3069972>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250304 |
| ECLASS-15.0 | 27250304 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002555 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 20122000 |
|-------------|----------|

# FTPR-3/15S - Test plug



3069972

<https://www.phoenixcontact.com/us/products/3069972>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | b3d4470c-bf82-43f2-adf8-ee99773ca2e8 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)