

DF-UP 4-CT/VT/ABB - Flange cover

3208676

<https://www.phoenixcontact.com/us/products/3208676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flange cover, snap onto the UP 4/... plugs, depth: 43.7 mm, width: 12.6 mm, height: 30.7 mm, color: light gray

The figure shows a similar product

Your advantages

- For reliable screw connection between the plug and screw flange
- The flange covers can be snapped onto the plug housing later on

Commercial data

Item number	3208676
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BE64
Product key	BE643X
GTIN	4046356152662
Weight per piece (including packing)	8.9 g
Weight per piece (excluding packing)	8.757 g
Customs tariff number	85389099
Country of origin	PL

DF-UP 4-CT/VT/ABB - Flange cover



3208676

<https://www.phoenixcontact.com/us/products/3208676>

Technical data

Connection data

Tightening torque	0.4 ... 0.5 Nm
-------------------	----------------

Dimensions

Width	12.6 mm
Height	30.7 mm
Depth	43.7 mm

Material specifications

Color	light gray (RAL 7035)
Material	PA
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

DF-UP 4-CT/VT/ABB - Flange cover

3208676

<https://www.phoenixcontact.com/us/products/3208676>



Classifications

UNSPSC

UNSPSC 21.0	39121425
-------------	----------

DF-UP 4-CT/VT/ABB - Flange cover



3208676

<https://www.phoenixcontact.com/us/products/3208676>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com