

DF-UP 4-CT/VT/ABB - Flange cover

3208676

<https://www.phoenixcontact.com/us/products/3208676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a similar product

Flange cover, snap onto the UP 4/... plugs, depth: 43.7 mm, width: 12.6 mm, height: 30.7 mm, color: light gray

Your advantages

- For reliable screw connection between the plug and screw flange
- The flange covers can be snapped onto the plug housing later on

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 3208676 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | BE64 |
| Product key | BE643X |
| GTIN | 4046356152662 |
| Weight per piece (including packing) | 8.9 g |
| Weight per piece (excluding packing) | 8.757 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

DF-UP 4-CT/VT/ABB - Flange cover



3208676

<https://www.phoenixcontact.com/us/products/3208676>

Technical data

Connection data

| | |
|-------------------|----------------|
| Tightening torque | 0.4 ... 0.5 Nm |
|-------------------|----------------|

Dimensions

| | |
|--------|---------|
| Width | 12.6 mm |
| Height | 30.7 mm |
| Depth | 43.7 mm |

Material specifications

| | |
|--|-----------------------|
| Color | light gray (RAL 7035) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

DF-UP 4-CT/VT/ABB - Flange cover

3208676

<https://www.phoenixcontact.com/us/products/3208676>



Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121425 |
|-------------|----------|

DF-UP 4-CT/VT/ABB - Flange cover



3208676

<https://www.phoenixcontact.com/us/products/3208676>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com