

UK 10,3 HESILED 1000V - Fuse holder

3211249

<https://www.phoenixcontact.com/us/products/3211249>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse holder, fuse type: Ceramic, fuse type: gPV 10.3 x 38 mm in accordance with 60269-6, nom. voltage: 1000 V DC, nominal current: 30 A, connection method: Screw connection, Rated cross section: 16 mm², cross section: 0.75 mm²- 25 mm², mounting type: NS 35/7,5, NS 35/15, color: black

Your advantages

- Quick identification of faulty fuses regardless of the current direction, thanks to LED status indicator
- For 10 x 38 gPV fuse-links in accordance with IEC 60269-6
- Fuse holder for fusing 400 V – 1000 V DC PV strings
- Easy to bridge

Commercial data

Item number	3211249
Packing unit	12 pc
Minimum order quantity	12 pc
Sales key	BE12
Product key	BE1234
GTIN	4046356482400
Weight per piece (including packing)	46.666 g
Weight per piece (excluding packing)	46.666 g
Customs tariff number	85369095
Country of origin	DE

UK 10,3 HESILED 1000V - Fuse holder



3211249

<https://www.phoenixcontact.com/us/products/3211249>

Technical data

Notes

Order information:	Fuse-link not supplied as standard
--------------------	------------------------------------

Product properties

Product type	Fuse terminal block
Number of connections	2
Number of rows	1

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Fuse type	Ceramic
Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	4 W
Fuse	gPV 10.3 x 38 mm in accordance with 60269-6

Connection data

Number of connections per level	2
Nominal cross section	16 mm ²
Connection method	Screw connection
Screw thread	M5
Tightening torque	2 ... 2.5 Nm
Stripping length	11 mm
Internal cylindrical gage	B6
Connection in acc. with standard	IEC 60269-1 / -2
Conductor cross-section rigid	0.75 mm ² ... 25 mm ²
Cross section AWG	16 ... 4 (converted acc. to IEC)
Conductor cross-section flexible	0.75 mm ² ... 25 mm ²
Conductor cross-section, flexible [AWG]	18 ... 4 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.75 mm ² ... 16 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.75 mm ² ... 16 mm ²
Cross-section with insertion bridge, rigid	10 mm ²
Cross-section with insertion bridge, flexible	10 mm ²
2 conductors with same cross section, rigid	0.75 mm ² ... 4 mm ²
2 conductors with same cross section, flexible	0.75 mm ² ... 4 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.75 mm ² ... 4 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.75 mm ² ... 10 mm ²
Nominal cross section	16 mm ²
Nominal current	30 A (the current and voltage are determined by the fuse)

UK 10,3 HESILED 1000V - Fuse holder



3211249

<https://www.phoenixcontact.com/us/products/3211249>

Maximum load current	30 A (the current and voltage are determined by the fuse)
Nominal voltage	1000 V DC (the current and voltage are determined by the fuse)

Dimensions

Width	17.6 mm
Height	79.3 mm
Depth on NS 35/7,5	64 mm
Depth on NS 35/15	71.5 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V2
Insulating material group	IIIb
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60269-1 / -2
----------------------------------	------------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15

Drawings

Circuit diagram



UK 10,3 HESILED 1000V - Fuse holder



3211249

<https://www.phoenixcontact.com/us/products/3211249>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3211249>

CSA Approval ID: 225908				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	1000 V	30 A	6 - 4	-

CSA Approval ID: 274201				
----------------------------	--	--	--	--

EAC Approval ID: KZ7500651131219505				
--	--	--	--	--

UK 10,3 HESILED 1000V - Fuse holder



3211249

<https://www.phoenixcontact.com/us/products/3211249>

Classifications

ECLASS

ECLASS-13.0	27250113
ECLASS-15.0	27250113

ETIM

ETIM 10.0	EC000899
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UK 10,3 HESILED 1000V - Fuse holder



3211249

<https://www.phoenixcontact.com/us/products/3211249>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.652 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com