

WP-G HF IP66 PG21 BK - Protective hose screw connection



3240892

<https://www.phoenixcontact.com/us/products/3240892>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable gland, Pg thread, IP66 protection, straight



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240892 |
| Packing unit | 25 pc |
| Minimum order quantity | 25 pc |
| Sales key | BF68 |
| Product key | AF7DSA |
| GTIN | 4046356709996 |
| Weight per piece (including packing) | 16.632 g |
| Weight per piece (excluding packing) | 16.71 g |
| Customs tariff number | 39174000 |
| Country of origin | DE |

WP-G HF IP66 PG21 BK - Protective hose screw connection



3240892

<https://www.phoenixcontact.com/us/products/3240892>

Technical data

Product properties

| | |
|------------------------------|----------------------------------|
| Product type | Protective hose screw connection |
| Application | Cable gland |
| Type of the screw connection | Conduit adapter |
| Cable outlet | straight |
| Thread type | Pg |

Dimensions

| | |
|--------------------------|---------|
| Width | 37 mm |
| Height | 48.5 mm |
| Wrench size | 34 mm |
| Wrench size for mounting | 34 mm |

External dimensions

| | |
|------------------|-------|
| Outside diameter | 23 mm |
|------------------|-------|

Material specifications

| | |
|--|--|
| Material | PA 6 |
| Flammability rating according to UL 94 | V0 |
| Material for screw connection | PA |
| Components | free from silicone, halogen, and cadmium |

Cable/line

| | |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

Mechanical properties

Mechanical data

| | |
|------------------------------|-----------------|
| Type of the screw connection | Conduit adapter |
|------------------------------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP66 |
| Ambient temperature (operation) | -40 °C ... 120 °C |
| Resistance to UV radiation | no |

WP-G HF IP66 PG21 BK - Protective hose screw connection



3240892

<https://www.phoenixcontact.com/us/products/3240892>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240892>



UL Recognized
Approval ID: E86359



LR



VDE approval of drawings

WP-G HF IP66 PG21 BK - Protective hose screw connection



3240892

<https://www.phoenixcontact.com/us/products/3240892>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27430311 |
| ECLASS-15.0 | 27430311 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001178 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

WP-G HF IP66 PG21 BK - Protective hose screw connection



3240892

<https://www.phoenixcontact.com/us/products/3240892>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 1.263 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com