

WP-BASE C PA HF 28,2 BK - Hose holder with cover



3240962

<https://www.phoenixcontact.com/us/products/3240962>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hose holder with cover, material: PA, color: black, flammability rating in acc. with UL 94: V2

Commercial data

Item number	3240962
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356710701
Weight per piece (including packing)	9.148 g
Weight per piece (excluding packing)	7.024 g
Customs tariff number	39174000
Country of origin	DE

WP-BASE C PA HF 28,2 BK - Hose holder with cover



3240962

<https://www.phoenixcontact.com/us/products/3240962>

Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Diameter	28.5 mm
Hole diameter	6.5 mm

Material specifications

Material	PA
Flammability rating according to UL 94	V2
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Mounting

Mounting type	Screw mounting
---------------	----------------

WP-BASE C PA HF 28,2 BK - Hose holder with cover



3240962

<https://www.phoenixcontact.com/us/products/3240962>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240962>



UL Recognized
Approval ID: E86359

WP-BASE C PA HF 28,2 BK - Hose holder with cover



3240962

<https://www.phoenixcontact.com/us/products/3240962>

Classifications

ECLASS

ECLASS-13.0	27430315
ECLASS-15.0	27430315

UNSPSC

UNSPSC 21.0	31162900
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.618 kg CO2e