

UM 56-REL 120VAC/1-1 HC - Active module



5601698

<https://www.phoenixcontact.com/us/products/5601698>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module with high-current relay

Commercial data

Item number	5601698
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK61Y2
GTIN	4046356687133
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85364190
Country of origin	US

UM 56-REL 120VAC/1-1 HC - Active module



5601698

<https://www.phoenixcontact.com/us/products/5601698>

Technical data

Notes

Trade restriction

CE note

The products are offered exclusively for export outside the EU and the European Economic Area.

Product properties

Product type

Multi-channel relay module

UM 56-REL 120VAC/1-1 HC - Active module



5601698

<https://www.phoenixcontact.com/us/products/5601698>

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

UM 56-REL 120VAC/1-1 HC - Active module



5601698

<https://www.phoenixcontact.com/us/products/5601698>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
---	---

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com