

MCR-SGA-LN-DC - Strain gage/load cell amplifier



5603007

<https://www.phoenixcontact.com/us/products/5603007>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Signal conditioner, low noise, for strain gage/load cell



The figure shows standard version

Product description

Universal low noise strain gage/load cell amplifier. 1.25 to 12-volt adjustable excitation, 0-5 V, 0-10 V, ± 5 V, ± 10 V and 4-20 mA output

Commercial data

Item number	5603007
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C401
Product key	DK1118
GTIN	4046356134286
Weight per piece (including packing)	184.6 g
Weight per piece (excluding packing)	184.6 g
Customs tariff number	85389091
Country of origin	US

5603007

<https://www.phoenixcontact.com/us/products/5603007>

Technical data

Product properties

Product type	Signal conditioner
--------------	--------------------

Electrical properties

Supply

Supply voltage range	11 V DC ... 30 V DC
Typical current consumption	105 mA
Max. current consumption	250 mA (350 W, full bridge at 10 V Excitation)

Input data

Signal

Description of the input	Excitation voltage
Voltage input signal	1.25 V ... 12 V
Max. current input signal	100 mA
Protective circuit	Short-circuit and thermal protection
Input impedance	10 GΩ
Bridge resistance	120 Ω ... 20000 Ω
Gain range	1 V ... 10000 V (13 steps)
Input range of the sensor	0.1 mV ... 1000 mV

Output data

Signal

Voltage output signal	0 V ... 5 V
	0 V ... 10 V
	-10 V ... 10 V
	-5 V ... 5 V
Current output signal	4 mA ... 20 mA

Connection data

Connection method	COMBICON plug-in screw terminal block
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Width	22.5 mm
Height	99 mm
Depth	111 mm

Environmental and real-life conditions

MCR-SGA-LN-DC - Strain gage/load cell amplifier



5603007

<https://www.phoenixcontact.com/us/products/5603007>

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	3300 m (Above sea level)
Permissible humidity (operation)	10 % ... 90 %

5603007

<https://www.phoenixcontact.com/us/products/5603007>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com