

# PI/NI-2I/I - Signal conditioner



5607189

<https://www.phoenixcontact.com/us/products/5607189>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



## Product description

The PI/NI-2I/I current limiter works with two-wire transmitters to prevent short circuit conditions in 4-20 mA loops and is particularly suited for use in hazardous areas. A short circuit condition is indicated by a status LED and each channel has a digital output for reporting to a control system, protected by optocoupler isolation.

## Commercial data

Item number	5607189
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN11
Product key	DNC1Z1
GTIN	4046356686822
Weight per piece (including packing)	67 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85439088
Country of origin	US

# PI/NI-2I/I - Signal conditioner



5607189

<https://www.phoenixcontact.com/us/products/5607189>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

#### Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

### Product properties

Product type	Signal conditioner
No. of channels	2

### Input data

#### Signal

Description of the input	Analog input
Number of inputs	2
Input signal	Current
Current input signal	4 mA ... 20 mA

### Output data

#### Signal:

Maximum switching voltage	24 V DC (+20 %)
Minimum switching voltage	24 V DC (-20 %)
Max. switching current	50 mA (alarm outputs)

#### Signal

Number of outputs	2
Current output signal	4 mA ... 20 mA

### Connection data

Connection method	Screw
Conductor cross-section AWG	30 ... 12
Tightening torque	5 lb <sub>F</sub> -in. ... 7 lb <sub>F</sub> -in.

### Ex data

#### Safety data

Max. output voltage $U_o$	24 V DC
Max. output current $I_o$	25 mA
Max. output power $P_o$	567 mW
Max. external inductivity $L_o$ / Max. external capacitance $C_o$	/ 600 $\mu$ F 420 mH

# PI/NI-2I/I - Signal conditioner



5607189

<https://www.phoenixcontact.com/us/products/5607189>

## Dimensions

Width	17 mm
Height	94 mm
Depth	70 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C

## Approvals

### Ex data

UL, USA / Canada	Class I, Zone 2, AEx nA [nC] IIC T4
	Class I, Zone 2, Ex nA [nL] IIC T4 X
	Class I, Div. 2, Groups A, B, C, D T4

# PI/NI-2I/I - Signal conditioner





5607189


<https://www.phoenixcontact.com/us/products/5607189>


## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5607189>

 <b>UL Listed</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
Output	24 V	-	30 - 10	30 - 10

 <b>cUL Listed</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
Output	24 V	-	30 - 10	-

 <b>cUL Listed</b> Approval ID: E199827				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
Output	24 V	0.02 A	30 - 12	-

 <b>UL Listed</b> Approval ID: E199827				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
Output	24 V	0.02 A	30 - 12	-

# PI/NI-2I/I - Signal conditioner



5607189

<https://www.phoenixcontact.com/us/products/5607189>

## Classifications

### ECLASS

ECLASS-13.0	27210120
ECLASS-15.0	27210120

### ETIM

ETIM 10.0	EC002653
-----------	----------

### UNSPSC

UNSPSC 21.0	39121000
-------------	----------

# PI/NI-2I/I - Signal conditioner



5607189

<https://www.phoenixcontact.com/us/products/5607189>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)