

# DIN rail, unperforated - NS 15 BLK UNPERF 2000MM VPE 10 - 1401789


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail, unperforated, acc. to EN 60715, material: Steel, uncoated, Standard profile, color: white aluminum, Pack of 10 (20 m)



## Key Commercial Data

|                        |   |
|------------------------|---|
| Packing unit           | 10 pc   |
| Minimum order quantity | 10 pc   |
| GTIN                   | <br>4 017918 155421 |
| GTIN                   | 4017918155421   |

## Technical data

### Dimensions

|        |         |
|--------|---------|
| Height | 5.5 mm  |
| Length | 2000 mm |
| Width  | 15 mm   |

### Standards and Regulations

|                                  |                  |
|----------------------------------|------------------|
| Test standard                    | acc. to EN 60715 |
| Connection in acc. with standard | IEC / EN         |


### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Drawings

# DIN rail, unperforated - NS 15 BLK UNPERF 2000MM VPE 10 - 1401789

Dimensional drawing



## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400602 |
| eCl@ss 11.0   | 27400602 |
| eCl@ss 4.0    | 27110800 |
| eCl@ss 4.1    | 27110800 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27400600 |
| eCl@ss 7.0    | 27400602 |
| eCl@ss 9.0    | 27400602 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001285 |
| ETIM 3.0 | EC001285 |
| ETIM 4.0 | EC000212 |
| ETIM 6.0 | EC001285 |
| ETIM 7.0 | EC001285 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212109 |
| UNSPSC 7.0901 | 39121708 |
| UNSPSC 11     | 39121708 |
| UNSPSC 12.01  | 39121708 |
| UNSPSC 13.2   | 39121708 |
| UNSPSC 18.0   | 39121708 |
| UNSPSC 19.0   | 39121708 |
| UNSPSC 20.0   | 39121708 |

Phoenix Contact 2022 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>