

## Feed-through header - ICC25-H/4R5,0-7035 - 2203903

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




PCB headers, number of positions: 4, pitch: 5 mm, color: light gray, Product with pin output on right side

### Your advantages

- ✓ Designed for integration into the wave soldering process
- ✓ Easy and fast push-in mounting of assembled printed-circuit boards, thanks to stable guide rails
- ✓ Variable coding, for reliable protection against incorrect connection



### Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	
GTIN	4055626466088

### Technical data

#### Dimensions

Length [ l ]	20.35 mm
Width	25 mm
Pitch	5 mm
Width [ w ]	25 mm
Height [ h ]	22.4 mm
Length of the solder pin	3.5 mm
Length	20.35 mm

#### General

Range of articles	ICC25-H/.R
Insulating material group	I
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV

# Feed-through header - ICC25-H/4R5,0-7035 - 2203903

## Technical data

### General

Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	250 V
Rated voltage (III/2)	320 V
Rated voltage (II/2)	630 V
Nominal current $I_N$	16 A
Insulating material	PA
Flammability rating according to UL 94	V0
Color	light gray
Number of positions	4

### Standards and Regulations


Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings


Diagram



Type: PSPT 2,5/...-ST ... with ICC20(25)-H/...L(R)5,0-...

# Feed-through header - ICC25-H/4R5,0-7035 - 2203903

Diagram



Type: MSTBT 2,5 HC/...-STF with ICC20(25)-H/...L(R)5,0-...

## Approvals

Approvals

Approvals

EAC / cULus Recognized

Ex Approvals

## Approval details

EAC		B.01742
-----	--	---------

cULus Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E60425-20181123
	B	D	
Nominal voltage UN	300 V	150 V	
Nominal current IN	16 A	15 A	

Phoenix Contact 2019 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>