

Front adapters - FLKM S135/42X0,75/3,0M/OE - 2315007


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Startup adapter for extending the existing S5-135 field wiring. Establishing all S5-135 connections (1 to 42, 42-pos.) to open cable end.

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 292962
GTIN	4046356292962

Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 80 °C
Degree of protection	IP20

General

Max. permissible operating voltage	250 V AC/DC
Max. permissible current	6 A (per path)
Mounting position	any

Connection data

Connection name	Controller level
Connection method	SIEMENS S5-135 U pin strip

Connection data 2

Connection name	Field level
Connection method	Single wires
Number of connections	42
Number of positions	1

Cable

Front adapters - FLKM S135/42X0,75/3,0M/OE - 2315007

Technical data

Cable

Conductor construction: Number of litz wires:	42
Single wire, material	Cu uninsulated
Single wire, cross section	0.75 mm²
Length of cable	3 m
Shielding	no
Halogen-free cable	No

Supported controller

Controller	SIEMENS S5-135 U
- suitable I/O card	6ES5 ...

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.A*30.B.01742
-----	--	--------------------------