

## Front adapters - FLKM S135/42X0,75/3,0M/OE - 2315007

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Startup adapter for extending the existing S5-135 field wiring. Establishing all S5-135 connections (1 to 42, 42-pos.) to open cable end.



### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356292962

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 80 °C
Degree of protection	IP20

#### General

Max. permissible operating voltage	250 V AC/DC
Max. permissible current	6 A (per path)
Mounting position	any

#### Connection data

Connection name	Controller level
Connection method	SIEMENS S5-135 U pin strip

#### Connection data 2

Connection name	Field level
Connection method	Single wires
Number of connections	42
Number of positions	1

# Front adapters - FLKM S135/42X0,75/3,0M/OE - 2315007

## Technical data

### Cable

Conductor construction: Number of litz wires:	42
Single wire, material	Cu uninsulated
Single wire, cross section	0.75 mm <sup>2</sup>
Length of cable	3 m
Shielding	no
Halogen-free cable	No

### Supported controller


Controller	SIEMENS S5-135 U
- suitable I/O card	6ES5 ...

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Circuit diagram



## Classifications

### eCl@ss

eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27250300
eCl@ss 5.1	27250300
eCl@ss 6.0	27249200
eCl@ss 7.0	27249290
eCl@ss 8.0	27249290
eCl@ss 9.0	27242292

### ETIM

ETIM 4.0	EC002584
ETIM 5.0	EC002584

## Front adapters - FLKM S135/42X0,75/3,0M/OE - 2315007

### Classifications

#### ETIM

ETIM 6.0	EC002584
ETIM 7.0	EC002584

#### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	32151601
UNSPSC 18.0	32151601
UNSPSC 19.0	32151601
UNSPSC 20.0	32151601
UNSPSC 21.0	32151601

### Approvals

#### Approvals

---

#### Approvals


#### EAC

---

#### Ex Approvals

---

#### Approval details

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>