

## Accessories - PTCM-MP-P 0,14-0,5 R - 1013778


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Tin

RoHS

### Key Commercial Data

Packing unit	5000 pc
Minimum order quantity	5000 pc
GTIN	 4 055626 493121
GTIN	4055626493121

### Technical data

#### General

Range of articles	PTCM-MP-P
-------------------	-----------

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27440204
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309
eCl@ss 8.0	27440204

# Accessories - PTCM-MP-P 0,14-0,5 R - 1013778

## Classifications

eCl@ss

eCl@ss 9.0	27440204
------------	----------

ETIM

ETIM 5.0	EC000796
ETIM 6.0	EC000796
ETIM 7.0	EC000796

## Approvals

Approvals

Approvals

EAC

Ex Approvals

### Approval details

EAC		B.01687
-----	--	---------

## Accessories

Accessories

Crimping tool

Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998



Crimping pliers, for COMBICON crimp connectors with cross section: 0.14 ... 0.75 mm<sup>2</sup>. Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. 2 positioning aids

## Additional products

Printed-circuit board connector - PTCM 0,5/ 2-PL-2,5 WH - 1015464



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 2, pitch: 2.5 mm, connection method: Crimp connection, color: white, contact surface: Tin

## Accessories - PTCM-MP-P 0,14-0,5 R - 1013778

### Accessories

---

#### Printed-circuit board connector - PTCM 0,5/ 3-PL-2,5 WH - 1015463



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 3, pitch: 2.5 mm, connection method: Crimp connection, color: white, contact surface: Tin

---

#### Printed-circuit board connector - PTCM 0,5/ 4-PL-2,5 WH - 1015462



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 4, pitch: 2.5 mm, connection method: Crimp connection, color: white, contact surface: Tin

---

#### Printed-circuit board connector - PTCM 0,5/ 5-PL-2,5 WH - 1015461



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 5, pitch: 2.5 mm, connection method: Crimp connection, color: white, contact surface: Tin

---

#### Printed-circuit board connector - PTCM 0,5/ 6-PL-2,5 WH - 1015460



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 6, pitch: 2.5 mm, connection method: Crimp connection, color: white, contact surface: Tin

---

#### Printed-circuit board connector - PTCM 0,5/ 7-PL-2,5 WH - 1015459



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 7, pitch: 2.5 mm, connection method: Crimp connection, color: white, contact surface: Tin

---

## Accessories - PTCM-MP-P 0,14-0,5 R - 1013778

### Accessories

#### Printed-circuit board connector - PTCM 0,5/ 8-PL-2,5 WH - 1015458



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 8, pitch: 2.5 mm, connection method: Crimp connection, color: white, contact surface: Tin

---

#### Printed-circuit board connector - PTCM 0,5/ 2-PL-2,5 BK - 1048116



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 2, pitch: 2.5 mm, connection method: Crimp connection, color: black, contact surface: Tin

---

#### Printed-circuit board connector - PTCM 0,5/ 3-PL-2,5 BK - 1048117



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 3, pitch: 2.5 mm, connection method: Crimp connection, color: black, contact surface: Tin

---

#### Printed-circuit board connector - PTCM 0,5/ 4-PL-2,5 BK - 1048118



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 4, pitch: 2.5 mm, connection method: Crimp connection, color: black, contact surface: Tin

---

#### Printed-circuit board connector - PTCM 0,5/ 5-PL-2,5 BK - 1048119



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 5, pitch: 2.5 mm, connection method: Crimp connection, color: black, contact surface: Tin

---

## Accessories - PTCM-MP-P 0,14-0,5 R - 1013778

### Accessories

Printed-circuit board connector - PTCM 0,5/ 6-PL-2,5 BK - 1048121



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 6, pitch: 2.5 mm, connection method: Crimp connection, color: black, contact surface: Tin

Printed-circuit board connector - PTCM 0,5/ 7-PL-2,5 BK - 1048122



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 7, pitch: 2.5 mm, connection method: Crimp connection, color: black, contact surface: Tin

Printed-circuit board connector - PTCM 0,5/ 8-PL-2,5 BK - 1048123



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.75 mm<sup>2</sup>, number of positions: 8, pitch: 2.5 mm, connection method: Crimp connection, color: black, contact surface: Tin

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>