

CUC-IND-C1ZNI-T/R4IP8 - RJ45 connector



1421128

<https://www.phoenixcontact.com/us/products/1421128>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 23- 22, cable outlet: angled, Ethernet/PROFINET

Your advantages

- Easy and time-saving assembly with IDC fast connection technology
- Can be used internationally due to EAC, UL 1863, and CAN/CSA C22.2
- Ideal companion for servicing or repairs in the field: no special tools required for mounting

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1421128 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB10 |
| Product key | ABNAAA |
| GTIN | 4055626254678 |
| Weight per piece (including packing) | 31.6 g |
| Weight per piece (excluding packing) | 17.186 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

CUC-IND-C1ZNI-T/R4IP8 - RJ45 connector



1421128

<https://www.phoenixcontact.com/us/products/1421128>

Technical data

Product properties

| | |
|----------------------|-----------------------------|
| Product type | Data connector (cable side) |
| Type | RJ45 |
| Sensor type | Ethernet/PROFINET |
| Number of positions | 8 |
| Connection profile | RJ45 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Cable outlet | angled |
| Positions/contacts | 8P8C |

Insulation characteristics

| | |
|----------------------|---|
| Overvoltage category | I |
| Degree of pollution | 2 |

Electrical properties

| | |
|---|---|
| Rated voltage (III/3) | 72 V (DC) |
| Rated current | 1.75 A |
| Contact resistance | < 20 m Ω (Contact) < 100 m Ω (shield) |
| Frequency range | to 100 MHz |
| Insulation resistance | > 500 M Ω |
| Nominal voltage U_N | 48 V |
| Nominal current I_N | 1.75 A |
| Contact resistance per contact pair | < 20 Ω |
| Contact resistance | > 10 m Ω (Wire – IDC) 0.005 Ω (Litz wires – IDC) |
| Transmission medium | Copper |
| Transmission speed | 1 Gbps |
| Transmission characteristics (category) | CAT5 |
| Transmission speed | 1 Gbps |
| Power transmission | PoE++ in accordance with: IEEE 802.3bt |

Connection data

Connection technology

| | |
|----------------------------------|---|
| Connection method | Insulation displacement connection |
| Connection cross section AWG | 23 ... 22 (solid) 23 ... 22 (flexible) |
| Conductor cross-section | 0.25 mm ² ... 0.34 mm ² (solid) 0.25 mm ² ... 0.34 mm ² (flexible) |
| Connection in acc. with standard | in accordance with IEC 60603-7-1 |

CUC-IND-C1ZNI-T/R4IP8 - RJ45 connector



1421128

<https://www.phoenixcontact.com/us/products/1421128>

Dimensions

| | |
|--------|---------|
| Width | 13.6 mm |
| Height | 41.2 mm |
| Length | 37.9 mm |

Material specifications

| | |
|--|-----------------|
| Material | Plastic |
| Flammability rating according to UL 94 | V0 |
| Housing material | Metal |
| Housing surface material | Ni |
| Cable seal material | NBR |
| Contact material | CuSn |
| Contact surface material | Au/Ni |
| Contact carrier material | PC |
| Locking latch material | Stainless steel |

Cable/line

| | |
|------------------------------------|----------------------|
| External cable diameter | 5 mm ... 9 mm |
| External cable diameter | 5 mm ... 9 mm |
| Wire diameter including insulation | ≤ 1.6 mm |
| Cable cross section | 0.23 mm ² |
| Test voltage Core/Core | 1000 V |
| Test voltage Core/Shield | 1500.00 V |

Mechanical properties

Mechanical data

| | |
|-------------------------------------|-----------|
| Insertion/withdrawal cycles | ≥ 750 |
| Insertion force per signal contact | < 20.00 N |
| Extraction force per signal contact | < 20 N |

Environmental and real-life conditions

Test specification

| | |
|---------------|------------------------|
| Type of test | Vibration test |
| Specification | IEC 60068-2-6 |
| Frequency | 10-500 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.35 mm |
| Acceleration | 50.00 m/s ² |
| Test duration | 20.00 s |

Mounting

| | |
|---------------|--------------------|
| Mounting type | For field assembly |
|---------------|--------------------|

CUC-IND-C1ZNI-T/R4IP8 - RJ45 connector



1421128

<https://www.phoenixcontact.com/us/products/1421128>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1421128>

|  cULus Recognized Approval ID: E335024-20170228 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 56.5 V | 1.75 A | - | - |

CUC-IND-C1ZNI-T/R4IP8 - RJ45 connector



1421128

<https://www.phoenixcontact.com/us/products/1421128>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440114 |
| ECLASS-15.0 | 27440114 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002636 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CUC-IND-C1ZNI-T/R4IP8 - RJ45 connector



1421128

<https://www.phoenixcontact.com/us/products/1421128>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com