

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Primary-switched power supply unit QUINT POWER, Screw connection, DIN rail mounting, SFB Technology (Selective Fuse Breaking), input: 1-phase, output: 24 V DC / 5 A, adjustable from 18 V DC ... 29.5 V DC. Please use the following item for new projects: 2904616 QUINT4-PS/1AC/24DC/10/+

## Product description

QUINT POWER power supplies with maximum functionality

QUINT POWER circuit breakers magnetically and therefore quickly trip at six times the nominal current, for selective and therefore cost-effective system protection. In addition, the high system availability is ensured by preventive function monitoring which reports critical operating states before errors can occur.

Reliable starting of heavy loads takes place via the static power reserve POWER BOOST. Thanks to the adjustable voltage, all ranges between 18 V DC ... 29.5 V DC are covered.

## Your advantages

- For superior system availability
- Reliable starting of difficult loads with the static POWER BOOST power reserve with up to 1.5 times the nominal current permanently
- Fast tripping of standard circuit breakers with dynamic power reserve SFB (selective fuse breaking) technology with up to 6 times the nominal current for 12 ms
- Preventive function monitoring
- Optimum protection with dip coating for 100 % humidity

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2320908       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CM11          |
| Product key                          | CMPQ13        |
| GTIN                                 | 4046356520010 |
| Weight per piece (including packing) | 1,081.3 g     |
| Weight per piece (excluding packing) | 777 g         |
| Customs tariff number                | 85044095      |
| Country of origin                    | TH            |

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

## Technical data

### Input data

#### AC operation

|  |  |
|--|--|
| Nominal input voltage range              | 100 V AC ... 240 V AC                          |
| Input voltage range                      | 85 V AC ... 264 V AC                           |
| Electric strength, max.                  | 300 V AC                                       |
| Voltage type of supply voltage           | AC   |
| Inrush current                           | < 15 A   |
| Inrush current integral ( $I^2t$ )       | < 1 A <sup>2</sup> s                           |
| Inrush current limitation                | 15 A   |
| AC frequency range                       | 45 Hz ... 65 Hz                                |
| Frequency range DC                       | 0 Hz   |
| Mains buffering time                     | typ. 55 ms (120 V AC)<br>typ. 55 ms (230 V AC) |
| Current consumption                      | 1.5 A (100 V AC)<br>0.6 A (240 V AC)           |
| Nominal power consumption                | 141 VA   |
| Protective circuit                       | Transient surge protection; Varistor           |
| Typical response time                    | < 0.15 s                                       |
| Input fuse                               | 5 A (slow-blow, internal)                      |
| Permissible backup fuse                  | B6 B10 B16 AC:                                 |
| Recommended breaker for input protection | 6 A ... 16 A (AC: Characteristics B, C, D, K)  |
| Discharge current to PE                  | < 3.5 mA                                       |

#### DC operation

|                                |  |
|--------------------------------|--|
| Nominal input voltage range    | 110 V DC ... 250 V DC                                      |
| Input voltage range            | 110 V DC ... 250 V DC -18 % ... +64 % (UL 508: ≤ 250 V DC) |
| Voltage type of supply voltage | DC   |
| Current consumption            | 1.3 A (110 V DC)<br>0.55 A (250 V DC)                      |

### Output data

|   |  |
|---|--|
| Efficiency  | typ. 88.3 % (120 V AC)<br>typ. 90 % (230 V AC)           |
| Nominal output voltage                            | 24 V DC ±1 %   |
| Setting range of the output voltage ( $U_{Set}$ ) | 18 V DC ... 29.5 V DC (> 24 V DC, constant capacity)     |
| Nominal output current ( $I_N$ )                  | 5 A (-25 °C ... 60 °C, $U_{OUT}$ = 24 V DC)              |
| POWER BOOST ( $I_{Boost}$ )                       | 7.5 A (-25 °C ... 40 °C permanent, $U_{OUT}$ = 24 V DC ) |
| Selective Fuse Breaking ( $I_{SFB}$ )             | 30 A (12 ms)   |
| Magnetic circuit breaker tripping                 | B2 / B4 / C2   |
| Derating  | 60 °C ... 70 °C (2.5 %/K)                                |

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

|  |   |
|--|---|
| Feedback voltage resistance                        | ≤ 35 V DC                                     |
| Protection against overvoltage at the output (OVP) | ≤ 32 V DC                                     |
| Control deviation                                  | < 1 % (change in load, static 10 % ... 90 %)  |
|  | < 2 % (change in load, dynamic 10 % ... 90 %) |
|  | < 0.1 % (change in input voltage ±10 %)       |
| Residual ripple                                    | < 40 mV <sub>PP</sub> (with nominal values)   |
| Output power                                       | 120 W   |
|  | 180 W   |
| Maximum no-load power dissipation                  | 3 W   |
| Power loss nominal load max.                       | 15 W  |
| Rise time  | < 0.1 s (U <sub>OUT</sub> (10 % ... 90 %))    |
| Connection in parallel                             | yes, for redundancy and increased capacity    |
| Connection in series                               | yes   |
| Fuse protection (secondary side)                   | electronic                                    |
|  | thermal-magnetic                              |
|  | thermal                                       |

Signal: DC OK active

|                         |   |
|-------------------------|---|
| Output description      | U <sub>OUT</sub> > 0.9 x U <sub>N</sub> : High signal |
| Switching voltage range | 18 V DC ... 24 V DC                                   |
| Maximum inrush current  | 20 mA (short-circuit-proof)                           |
| Continuous load current | ≤ 20 mA   |

Signal: DC OK floating

|                           |   |
|---------------------------|---|
| Output description        | Relay contact, U <sub>OUT</sub> > 0.9 x U <sub>N</sub> : Contact closed |
| Maximum switching voltage | 30 V AC   |
|                           | 24 V DC   |
| Maximum inrush current    | 0.5 A (ATEX/IECEX: Ohmic loads only)                                    |
|                           | 1 A (ATEX/IECEX: Ohmic loads only)                                      |
| Continuous load current   | 1 A   |

Signal: POWER BOOST, active

|                         |   |
|-------------------------|---|
| Output description      | I <sub>OUT</sub> < I <sub>N</sub> : High signal |
| Switching voltage range | 18 V DC ... 24 V DC                             |
| Output voltage          | + 24 V DC                                       |
| Maximum inrush current  | 20 mA (short-circuit-proof)                     |
| Continuous load current | ≤ 20 mA   |

## Connection data

Input

|                                     |                     |
|-------------------------------------|---------------------|
| Connection method                   | Screw connection    |
| Conductor cross-section, rigid min. | 0.2 mm <sup>2</sup> |
| Conductor cross-section, rigid max. | 2.5 mm <sup>2</sup> |

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

|                                       |                     |
|---------------------------------------|---------------------|
| Conductor cross-section flexible min. | 0.2 mm <sup>2</sup> |
| Conductor cross-section flexible max. | 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG min.      | 20                  |
| Conductor cross-section AWG max.      | 12                  |
| Stripping length                      | 7 mm                |
| Screw thread                          | M3                  |
| Tightening torque, min                | 0.5 Nm              |
| Tightening torque max                 | 0.6 Nm              |

## Output

|                                       |                     |
|---------------------------------------|---------------------|
| Connection method                     | Screw connection    |
| Conductor cross-section, rigid min.   | 0.2 mm <sup>2</sup> |
| Conductor cross-section, rigid max.   | 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible min. | 0.2 mm <sup>2</sup> |
| Conductor cross-section flexible max. | 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG min.      | 20                  |
| Conductor cross-section AWG max.      | 12                  |
| Stripping length                      | 7 mm                |
| Screw thread                          | M3                  |
| Tightening torque, min                | 0.5 Nm              |
| Tightening torque max                 | 0.6 Nm              |

## Signal

|                                       |                     |
|---------------------------------------|---------------------|
| Conductor cross-section, rigid min.   | 0.2 mm <sup>2</sup> |
| Conductor cross-section, rigid max.   | 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible min. | 0.2 mm <sup>2</sup> |
| Conductor cross-section flexible max. | 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG min.      | 20                  |
| Conductor cross-section AWG max.      | 12                  |
| Screw thread                          | M3                  |
| Tightening torque, min                | 0.5 Nm              |
| Tightening torque max                 | 0.6 Nm              |

## Signaling

|                    |                         |
|--------------------|-------------------------|
| Types of signaling | LED                     |
|                    | Active switching output |
|                    | Relay contact           |

## Signal output: DC OK active

|                        |   |
|------------------------|---|
| Status display         | $U_{OUT} > 0.9 \times U_N$ : "DC OK" LED green    |
| Note on status display | $U_{OUT} < 0.9 \times U_N$ : Flashing "DC OK" LED |
|                        | $I_{OUT} < I_N$ : LED ON                          |
| Color                  | green   |
| Note on status display | LED flashing                                      |

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

## Signal output: DC OK floating

|                        |   |
|------------------------|---|
| Status display         | $U_{OUT} > 0.9 \times U_N$ : "DC OK" LED green    |
| Note on status display | $U_{OUT} < 0.9 \times U_N$ : Flashing "DC OK" LED |
| Color                  | green   |
| Note on status display | LED flashing                                      |

## Signal output: POWER BOOST, active

|                |                                      |
|----------------|--------------------------------------|
| Status display | $I_{OUT} > I_N$ : LED "BOOST" yellow |
| Color          | yellow                               |

## Electrical properties

|                                 |                         |
|---------------------------------|-------------------------|
| Number of phases                | 1                       |
| Insulation voltage input/output | 4 kV AC (type test)     |
|                                 | 2 kV AC (routine test)  |
| Insulation voltage output / PE  | 850 V DC (routine test) |
| Insulation voltage input / PE   | 3.5 kV AC (type test)   |
|                                 | 2 kV AC (routine test)  |

## Product properties

|                            |                     |
|----------------------------|---------------------|
| Product type               | Power supply        |
| Product family             | QUINT POWER         |
| MTBF (IEC 61709, SN 29500) | > 1134000 h (25 °C) |
|                            | > 635000 h (40 °C)  |

## Insulation characteristics

|                                   |                      |
|-----------------------------------|----------------------|
| Protection class                  | I                    |
| Overvoltage category (EN 61010-1) | II ( $\leq 5000$ m)  |
| Overvoltage category (EN 62477-1) | III ( $\leq 2000$ m) |
| Degree of pollution               | 2                    |

## Dimensions

|        |        |
|--------|--------|
| Width  | 40 mm  |
| Height | 130 mm |
| Depth  | 125 mm |

## Installation dimensions

|                                  |               |
|----------------------------------|---------------|
| Installation distance right/left | 5 mm / 5 mm   |
| Installation distance top/bottom | 50 mm / 50 mm |

## Alternative assembly

|        |        |
|--------|--------|
| Width  | 122 mm |
| Height | 130 mm |
| Depth  | 43 mm  |

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

## Mounting

|                         |   |
|-------------------------|---|
| Mounting type           | DIN rail mounting   |
| Assembly note           | alignable: $P_N \geq 50\%$ , 5 mm horizontally, 15 mm next to active components, 50 mm vertically<br>alignable: $P_N < 50\%$ , 0 mm horizontally, 40 mm vertically top, 20 mm vertically bottom |
| Mounting position       | horizontal DIN rail NS 35, EN 60715   |
| With protective coating | yes   |

## Material specifications

|                      |   |
|----------------------|---|
| Housing material     | Metal   |
| Hood version         | Galvanized sheet steel, free from chrome (VI) |
| Side element version | Aluminum                                      |

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Degree of protection                           | IP20   |
| Ambient temperature (operation)                | -40 °C ... 70 °C (> 60 °C Derating: 2,5 %/K)   |
| Ambient temperature (storage/transport)        | -40 °C ... 85 °C   |
| Maximum altitude                               | ≤ 5000 m   |
| Climatic class                                 | 3K22 (in accordance with EN 60721-3-3)   |
| Max. permissible relative humidity (operation) | 100 % (at 25 °C, non-condensing)   |
| Shock  | 18 ms, 30g, in each space direction (according to IEC 60068-2-27)                          |
| Vibration (operation)                          | < 15 Hz, amplitude ±2.5 mm (according to IEC 60068-2-6)<br>15 Hz ... 150 Hz, 2.3g, 90 min. |
| Temp code                                      | T4 (-40 ... +60 °C)  |

## Standards and regulations

|  |                                    |
|--|------------------------------------|
| Rail applications  | EN 50121-4                         |
|  | EN 50121-3-2                       |
|  | EN 50124-1                         |
|  | EN 50155                           |
| HART FSK Physical Layer Test Specification Compliance                        | Output voltage $U_{Out}$ compliant |
| Standard – Limitation of mains harmonic currents                             | EN 61000-3-2                       |
| Standard - Electrical safety   | IEC 61010-2-201 (SELV)             |
| Explosive atmosphere   | EN 60079-0                         |
|  | EN 60079-7                         |
|  | EN 60079-15                        |
| Standard - Equipment safety  | BG (design tested)                 |
| Standard - Safe isolation  | IEC 61010-2-201                    |
| Standard - safety for equipment for measurement, control, and laboratory use | IEC 61010-1                        |

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

|  |  |
|--|--|
| Noxious gas test   | ISA-S71.04-1985 G3 Harsh Group A           |
| Approval - requirement of the semiconductor industry with regard to mains voltage dips | SEMI F47-0706 Compliance Certificate       |
| DeviceNet approval   | DeviceNet™ Power Supply Conformance Tested |

## Fire protection in rail vehicles

|                          |                                  |
|--------------------------|----------------------------------|
| Standard designation     | Fire protection in rail vehicles |
| Standards/specifications | EN 45545-2 (HL3)                 |

## Safety extra-low voltage

|                          |                          |
|--------------------------|--------------------------|
| Standard designation     | Safety extra-low voltage |
| Standards/specifications | IEC 61010-1 (SELV)       |

## Protective extra-low voltage

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | Protective extra-low voltage |
| Standards/specifications | IEC 61010-2-201 (PELV)       |

## Approvals

|                       |   |
|-----------------------|---|
| CSA                   | CAN/CSA-C22.2 No. 60950-1-07  |
|                       | CSA-C22.2 No. 107.1-01  |
| Shipbuilding approval | DNV (EMC A)   |
| SIQ                   | CB-Scheme (IEC 62368-1, IEC 61010-1, IEC 61010-2-201)                               |
| UL approvals          | UL/C-UL listed UL 508   |
|                       | UL/C-UL Recognized UL 60950-1   |
|                       | UL ANSI/ISA-12.12.01 Class I, Division 2, Groups A, B, C, D T4 (Hazardous Location) |
| DeviceNet approval    | DeviceNet™ Power Supply Conformance Tested  |

## INMETRO

|                |                    |
|----------------|--------------------|
| Identification | Ex ec nC IIC T4 Gc |
| Certificate    | DNV 19.0188 X      |

## ATEX

|                |                             |
|----------------|-----------------------------|
| Identification | ⊕ II 3 G Ex ec nC IIC T4 Gc |
| Certificate    | TÜV 11 ATEX 555674 X        |

## IECEX

|                |                    |
|----------------|--------------------|
| Identification | Ex ec nC IIC T4 Gc |
| Certificate    | IECEX TUN 11.0002X |

## EMC data

|                                     |   |
|-------------------------------------|---|
| Electromagnetic compatibility       | Conformance with EMC Directive 2014/30/EU         |
| Low Voltage Directive               | Conformance with Low Voltage Directive 2014/35/EC |
| EMC requirements for noise emission | EN 61000-6-3                                      |
|                                     | EN 61000-6-4                                      |
| EMC requirements for noise immunity | EN 61000-6-1                                      |

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

|                            |                                    |
|----------------------------|------------------------------------|
|                            | EN 61000-6-2                       |
| Noise emission             |                                    |
| Standards/regulations      | EN 55011 (EN 55022)                |
| Electrostatic discharge    |                                    |
| Standards/regulations      | EN 61000-4-2                       |
| Electrostatic discharge    |                                    |
| Contact discharge          | 8 kV (Test Level 4)                |
| Discharge in air           | 15 kV (Test Level 4)               |
| Comments                   | Criterion A                        |
| Electromagnetic HF field   |                                    |
| Standards/regulations      | EN 61000-4-3                       |
| Electromagnetic HF field   |                                    |
| Frequency range            | 80 MHz ... 1 GHz                   |
| Test field strength        | 20 V/m (Test Level 3)              |
| Frequency range            | 1 GHz ... 6 GHz                    |
| Test field strength        | 10 V/m (Test Level 3)              |
| Comments                   | Criterion A                        |
| Fast transients (burst)    |                                    |
| Standards/regulations      | EN 61000-4-4                       |
| Fast transients (burst)    |                                    |
| Input                      | 4 kV (Test Level 4 - asymmetrical) |
| Output                     | 2 kV (Test Level 3 - asymmetrical) |
| Signal                     | 2 kV (Test Level 4 - asymmetrical) |
| Comments                   | Criterion A                        |
| Surge voltage load (surge) |                                    |
| Standards/regulations      | EN 61000-4-5                       |
| Surge voltage load (surge) |                                    |
| Input                      | 2 kV (Test Level 3 - symmetrical)  |
|                            | 4 kV (Test Level 4 - asymmetrical) |
| Output                     | 1 kV (Test Level 2 - symmetrical)  |
|                            | 2 kV (Test Level 3 - asymmetrical) |
| Signal                     | 1 kV (Test Level 2 - asymmetrical) |
| Comments                   | Criterion A                        |
| Conducted interference     |                                    |
| Standards/regulations      | EN 61000-4-6                       |
| Conducted interference     |                                    |
| Input/output/signal        | asymmetrical                       |

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

|                 |                     |
|-----------------|---------------------|
| Frequency range | 0.15 MHz ... 80 MHz |
| Comments        | Criterion A         |
| Voltage         | 10 V (Test Level 3) |

## Emitted interference

|  |  |
|--|--|
| Standards/regulations                            | EN 61000-6-3   |
| Radio interference voltage in acc. with EN 55011 | EN 55011 (EN 55022) Class B, area of application: Industry and residential |
| Emitted radio interference in acc. with EN 55011 | EN 55011 (EN 55022) Class B, area of application: Industry and residential |

## Criteria

|             |  |
|-------------|--|
| Criterion A | Normal operating behavior within the specified limits.                               |
| Criterion B | Temporary impairment to operational behavior that is corrected by the device itself. |



# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2320908>



**cUL Recognized**  
Approval ID: E211944



**UL Recognized**  
Approval ID: E211944



**IECEE CB Scheme**  
Approval ID: SI-6188 A1



**EAC**  
Approval ID: RU S-DE.BL08.W.00764



**UL Listed**  
Approval ID: E123528



**Type approved**  
Approval ID: SI-SIQ BG 005/004

**DNV**

Approval ID: TAA000030X



**cCSAus**  
Approval ID: 1897779

**BIS Licence Document**

Approval ID: R-41268801



**EAC Ex**  
Approval ID: KZ 7500525010102094



**IECEx**  
Approval ID: IECEx TUN 11.0002X

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>



**cUL Listed**

Approval ID: E199827



**UL Listed**

Approval ID: E199827



**KC-s**

Approval ID: 20-KA4BO-0145X

**INMETRO**

Approval ID: DNV 19.0188 X



**ATEX**

Approval ID: TUEV 11ATEX555674 X



**NEPSI-EX**

Approval ID: GYJ20.1322X



**CCC**

Approval ID: 2020322303000836

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27040701 |
| ECLASS-15.0 | 27040701 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002540 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

# QUINT-PS/1AC/24DC/ 5/CO - Power supply, with protective coating



2320908

<https://www.phoenixcontact.com/us/products/2320908>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-25   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | fbca597d-2ac2-4ff0-9b8b-f31fbf969bb0 |

### EF3.1 Climate Change

|         |                |
|---------|----------------|
| CO2e kg | 30.706 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)