

USK 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



0271017

<https://www.phoenixcontact.com/us/products/0271017>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 800 V, nominal current: 32 A, number of connections: 8, connection method: Spade connection, Rated cross section: 4 mm², 1 level, cross section: 0.5 mm² - 6 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Commercial data

Item number	0271017
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE05
Product key	BE511X
GTIN	4017918000127
Weight per piece (including packing)	6.144 g
Weight per piece (excluding packing)	6.125 g
Customs tariff number	85369010
Country of origin	PL

USK 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



0271017

<https://www.phoenixcontact.com/us/products/0271017>

Technical data

Product properties

Product type	Feed-through terminal block
Number of connections	8
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.02 W

Connection data

Number of connections per level	8
Nominal cross section	4 mm ²

1 level

Connection method	Spade connection
Screw thread	M3
Spade connection	6.3/2.8 x 0.8 mm
Conductor cross-section rigid	0.5 mm ² ... 6 mm ²
Cross section AWG	20 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 6 mm ²
Conductor cross-section, flexible [AWG]	20 ... 10 (converted acc. to IEC)
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 6 mm ²
Nominal cross section	4 mm ²
Nominal current	32 A (current data for slip-on connections in acc. with EN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross-section.)
Maximum load current	32 A (current data for slip-on connections in acc. with EN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross-section.)
Nominal voltage	800 V (voltage data for slip-on connections in acc. with EN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross-section.)

Dimensions

Width	6.2 mm
End cover width	1.3 mm
Height	42.5 mm
Depth on NS 32	50.5 mm
Depth on NS 35/7,5	45.5 mm

USK 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



0271017

<https://www.phoenixcontact.com/us/products/0271017>

Depth on NS 35/15	53 mm
-------------------	-------

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

USK 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



0271017

<https://www.phoenixcontact.com/us/products/0271017>

Drawings

Circuit diagram



USK 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



0271017

<https://www.phoenixcontact.com/us/products/0271017>

Classifications

ECLASS

ECLASS-13.0

27250101

ETIM

ETIM 9.0

EC000897

UNSPSC

UNSPSC 21.0

39121400

USK 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



0271017

<https://www.phoenixcontact.com/us/products/0271017>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com