


USLKG 50-IB - Protective conductor terminal block



0443078

<https://www.phoenixcontact.com/us/products/0443078>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective conductor terminal block, with Allen screws, number of connections: 2, number of positions: 1, connection method: Screw connection, Rated cross section: 50 mm², cross section: 16 mm² - 50 mm², mounting method: PE foot with mounting screw, M6, mounting type: NS 35/7,5, NS 35/15, NS 32, color: green-yellow

Commercial data

Item number	0443078
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BE1221
GTIN	4017918002312
Weight per piece (including packing)	185 g
Weight per piece (excluding packing)	185 g
Country of origin	PL

USLKG 50-IB - Protective conductor terminal block



0443078

<https://www.phoenixcontact.com/us/products/0443078>

Technical data

Product properties

Product type	Ground terminal block
Product family	USLKG
Number of positions	1
Number of connections	2
Number of rows	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	4.73 W

Connection data

Grounding foot	Yes
Number of connections per level	2
Nominal cross section	50 mm ²

Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M6
Note	Please observe the current carrying capacity of the DIN rails.
Tightening torque	6 ... 8 Nm
Stripping length	24 mm
Connection in acc. with standard	IEC 60947-7-2
Conductor cross-section rigid	16 mm ² ... 50 mm ²
Cross section AWG	4 ... 2 (converted acc. to IEC)
Conductor cross-section flexible	25 mm ² ... 50 mm ²
Conductor cross-section, flexible [AWG]	2 ... 2 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	25 mm ² ... 50 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	25 mm ² ... 50 mm ²
Nominal cross section	50 mm ²
Connection in acc. with standard	IEC/EN 60079-7
Conductor cross-section rigid	16 mm ² ... 50 mm ²
Cross section AWG	6 ... 1/0 (converted acc. to IEC)
Conductor cross-section flexible	25 mm ² ... 50 mm ²

Ex data

Rated data (ATEX/IECEX)

Identification	Ⓜ II 2 GD Ex eb IIC Gb
----------------	------------------------

USLKG 50-IB - Protective conductor terminal block



0443078

<https://www.phoenixcontact.com/us/products/0443078>

Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	1203343 VDE-ISS 5
	1201659 E/AL-NS 32
	1201662 E/AL-NS 35
Torque range for PE foot	6 Nm ... 8 Nm
output	(Permanent)

Ex connection data General

Torque range	6 Nm ... 8 Nm
Nominal cross section	50 mm ²
Rated cross section AWG	1/0
Connection capacity rigid	16 mm ² ... 50 mm ²
Connection capacity AWG	6 ... 1/0
Connection capacity flexible	25 mm ² ... 50 mm ²
Connection capacity AWG	4 ... 1/0

Dimensions

Width	20 mm
Height	70.5 mm
Depth on NS 32	81 mm
Depth on NS 35/15	83.5 mm

Material specifications

Color	green-yellow
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

General

Terminal block mounting	6 Nm ... 8 Nm (PE foot with mounting screw, M6)
-------------------------	---

Mechanical data

USLKG 50-IB - Protective conductor terminal block



0443078

<https://www.phoenixcontact.com/us/products/0443078>

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-2
	IEC/EN 60079-7

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32
Terminal block mounting	6 Nm ... 8 Nm (PE foot with mounting screw, M6)

USLKG 50-IB - Protective conductor terminal block



0443078

<https://www.phoenixcontact.com/us/products/0443078>

Drawings

Circuit diagram



USLKG 50-IB - Protective conductor terminal block



0443078

<https://www.phoenixcontact.com/us/products/0443078>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0443078>



LR

Approval ID: LR2420186TA



CSA

Approval ID: 13631

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B	600 V	-	6 - 1/0	-
C	600 V	-	6 - 1/0	-
D	600 V	-	6 - 1/0	-



ATEX

Approval ID: KEMA99ATEX4487U



EAC Ex

Approval ID: KZ 7500525010101950



IEC Ex

Approval ID: IECExKEM06.0035U



UKCA-EX

Approval ID: DEKRA 21UKEX0308U

USLKG 50-IB - Protective conductor terminal block



0443078

<https://www.phoenixcontact.com/us/products/0443078>

Classifications

ECLASS

ECLASS-13.0	27250103
ECLASS-15.0	27250103

ETIM

ETIM 10.0	EC000901
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

USLKG 50-IB - Protective conductor terminal block



0443078

<https://www.phoenixcontact.com/us/products/0443078>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	2.057 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com