

# CT-TERMIBLOCK 10 DA - Screw termination block



0441711

<https://www.phoenixcontact.com/us/products/0441711>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw termination block with disconnect contacts for accommodating protective plugs CT and CTM. Use in MCR and telecommunications systems. Design: 10 double wires

## Your advantages

- Space-saving due to compact design
- Flexible fields of application with modular protective plug
- Maximum ease of maintenance, thanks to the 2-piece design

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0441711       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CL03          |
| Product key                          | CL321Z        |
| GTIN                                 | 4017918002213 |
| Weight per piece (including packing) | 172 g         |
| Weight per piece (excluding packing) | 167.6 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

# CT-TERMIBLOCK 10 DA - Screw termination block



0441711

<https://www.phoenixcontact.com/us/products/0441711>

## Technical data

### Product properties

|                       |                         |
|-----------------------|-------------------------|
| Product type          | Screw termination block |
| Product family        | COMTRAB                 |
| Type                  | LSA-PLUS module         |
| Wire pairs per module | 10                      |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 3   |

### Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Screw terminal blocks                       |
| Screw thread                     | M3  |
| Tightening torque                | 0.5 Nm                                      |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 12                                   |

### Dimensions

|                     |         |
|---------------------|---------|
| Dimensional drawing |         |
| Width               | 118 mm  |
| Height              | 43 mm   |
| Depth               | 40.9 mm |

### Material specifications

|  |                  |
|--|------------------|
| Color                                  | black (RAL 9005) |
| Flammability rating according to UL 94 | V2               |
| Insulating material group              | I / 600          |
| Housing material                       | PA               |
| Contact material                       | Cu alloy         |
| Contact surface material               | Sn               |

### Mechanical properties

#### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

# CT-TERMIBLOCK 10 DA - Screw termination block



0441711

<https://www.phoenixcontact.com/us/products/0441711>

## Protective circuit

|  |          |
|--|----------|
| Maximum continuous operating voltage $U_C$ | 240 V AC |
| Operating effective current $I_C$ at $U_C$ | 5 A      |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Degree of protection            | IP20             |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Altitude                        | 2000 m           |

## Standards and regulations

### Air clearances and creepage distances

|                       |             |
|-----------------------|-------------|
| Standards/regulations | IEC 60664-1 |
|-----------------------|-------------|

## Mounting

|               |                 |
|---------------|-----------------|
| Mounting type | DIN rail: 35 mm |
|---------------|-----------------|


# CT-TERMIBLOCK 10 DA - Screw termination block

0441711

<https://www.phoenixcontact.com/us/products/0441711>

## Drawings

Dimensional drawing



# CT-TERMIBLOCK 10 DA - Screw termination block



0441711

<https://www.phoenixcontact.com/us/products/0441711>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0441711>



**UL Listed**

Approval ID: FILE E 138168

# CT-TERMIBLOCK 10 DA - Screw termination block



0441711

<https://www.phoenixcontact.com/us/products/0441711>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27171503 |
| ECLASS-15.0 | 27171503 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001466 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

0441711

<https://www.phoenixcontact.com/us/products/0441711>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | aaa0c986-685f-4ef5-af1a-9d9e9bcaec17 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)