


OTTA 25-M5 - Feed-through terminal block



0790488

<https://www.phoenixcontact.com/us/products/0790488>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Universal terminal block with bolt connection, cross section: 0.1 - 25 mm², width: 18 mm, color: gray

Commercial data

Item number	0790488
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE45
Product key	BE4513
GTIN	4017918005597
Weight per piece (including packing)	54.242 g
Weight per piece (excluding packing)	54.242 g
Customs tariff number	85369010
Country of origin	IN

OTTA 25-M5 - Feed-through terminal block



0790488

<https://www.phoenixcontact.com/us/products/0790488>

Technical data

Product properties

Product type	Bolt connection terminal block
Product family	OTTA
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	3.26 W

Connection data

Number of connections per level	2
Nominal cross section	25 mm ²

Level 1 above 1 below 1

Connection method	Bolt connection
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal cross section	25 mm ²
Nominal current	101 A
Maximum load current	101 A (with 25 mm ² conductor cross-section)
Nominal voltage	800 V (the nominal voltage applies to insulated cable lugs)

Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	0.1 mm ² ... 25 mm ²
Cross section range AWG	16 ... 4 (converted acc. to IEC)
Hole diameter	5.3 mm
Width	16 mm
Bolt diameter	5 mm
Screw thread	M5
Tightening torque	2.5 ... 3 Nm
Connection in acc. with standard	DIN 46237:1970-07
Cross section	1 mm ² ... 6 mm ²
Cross section range AWG	(converted acc. to IEC)
Hole diameter	5.3 mm
Width	16 mm

OTTA 25-M5 - Feed-through terminal block



0790488

<https://www.phoenixcontact.com/us/products/0790488>

Bolt diameter	5 mm
Screw thread	M5
Tightening torque	2.5 ... 3 Nm

Dimensions

Width	18 mm
End cover width	2 mm
Height	60 mm
Depth on NS 32	69.5 mm
Depth on NS 35/7,5	64.5 mm
Depth on NS 35/15	72 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature \leq 45 K
Result	Test passed
Short-time withstand current 25 mm ²	3 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2 kV
Result	Test passed

Mechanical properties

Mechanical data

OTTA 25-M5 - Feed-through terminal block



0790488

<https://www.phoenixcontact.com/us/products/0790488>

Open side panel	Yes
-----------------	-----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 32/NS 35
Test force setpoint	10 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 (+/- 2) rpm
Revolutions	135
Conductor cross-section/weight	25 mm ² / 4.5 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2018-05
Spectrum	Long life test category 2, bogie-mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	6.12 (m/s ²) ² /Hz
Acceleration	3.12g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Pulse shape	Half-sine
Acceleration	5g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C

OTTA 25-M5 - Feed-through terminal block



0790488

<https://www.phoenixcontact.com/us/products/0790488>

Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

OTTA 25-M5 - Feed-through terminal block

0790488

<https://www.phoenixcontact.com/us/products/0790488>



Drawings

Circuit diagram




OTTA 25-M5 - Feed-through terminal block

0790488

<https://www.phoenixcontact.com/us/products/0790488>

Circuit diagram



- a = open
- 1 = cover
- 2 = insertion bridge
- 4 = partition plate

OTTA 25-M5 - Feed-through terminal block





0790488


<https://www.phoenixcontact.com/us/products/0790488>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0790488>

 CSA Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	100 A	18 - 4	-

 UL Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	600 V	115 A	-	-
C				
	600 V	115 A	-	-

 EAC Approval ID: RU C-DE.BL08.B.00540				
---	--	--	--	--

 EAC Approval ID: KZ7500651131219505				
---	--	--	--	--

DNV Approval ID: TAE0001CT				
--------------------------------------	--	--	--	--

OTTA 25-M5 - Feed-through terminal block



0790488

<https://www.phoenixcontact.com/us/products/0790488>

Classifications

ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

OTTA 25-M5 - Feed-through terminal block



0790488

<https://www.phoenixcontact.com/us/products/0790488>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com