

# SK U YE:UNGESTANZT - Marker sheet




0800132

<https://www.phoenixcontact.com/us/products/0800132>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker sheet, Din A4, yellow (RAL 1018), unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, Number of individual labels: 1, text field height: 296 mm, text field width: 210 mm



## Your advantages

- The unperforated SK-U... sheets are available for custom label designs
- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements
- Can be printed on all commercially available laser printers
- These labels have been specially developed for laser printers

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0800132       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG12          |
| Product key                          | BG2114        |
| GTIN                                 | 4017918005740 |
| Weight per piece (including packing) | 16.3 g        |
| Weight per piece (excluding packing) | 15.71 g       |
| Customs tariff number                | 39199080      |
| Country of origin                    | DE            |

## Technical data

### Notes

|         |   |
|---------|---|
| General | Print image may vary depending on laser printer |
|---------|---|

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Terminal marker |
|--------------|-----------------|

### Marking

|                             |                       |
|-----------------------------|-----------------------|
| Number of individual labels | 1                     |
| Identification technology   | Office laser printing |

### Dimensions

|        |           |
|--------|-----------|
| Width  | 210.00 mm |
| Height | 297.00 mm |
| Depth  | 0.32 mm   |

### Text field

|                   |        |
|-------------------|--------|
| Text field width  | 210 mm |
| Text field height | 296 mm |

### Material specifications

|                       |                   |
|-----------------------|-------------------|
| Foil strength         | 50 µm             |
| Adhesive strength     | 20 µm             |
| Adhesive              | Acrylic           |
| Color                 | yellow (RAL 1018) |
| Base element material | Polyester         |

### Environmental and real-life conditions

#### Ambient conditions

|   |                  |
|---|------------------|
| Ambient temperature (operation)                     | -20 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 20 °C            |
| Recommended humidity (storage/transport)            | 40 %             |

#### Test for substances that would hinder coating with paint or varnish

|   |                    |
|---|--------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364:2018-05 |
| Result  | Test passed        |

#### Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

#### Tesafilm test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
|---------------|-------------------------------------|

0800132

<https://www.phoenixcontact.com/us/products/0800132>

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 125 °C (150 °C) | Test passed                     |

## Wipe resistance of inscriptions

|   |  |
|---|--|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                       | Test passed  |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed  |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed  |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed  |

## Immersion in chemicals, oil &amp; fuel

|   |                          |
|---|--------------------------|
| Specification                                 | ISO 175:2010 (following) |
| Test duration                                 | 168 h                    |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ] | Test passed              |
| Ethanol (99 %)<br>[CAS No. 64-17-5]           | Test passed              |
| Diesel<br>[CAS No. 68476-34-6]                | Test passed              |
| IRM 901                                       | Test passed              |
| IRM 902                                       | Test passed              |
| IRM 903                                       | Test passed              |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                          |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result        | Test passed              |
| Procedure     | Method B                 |
| Cycles        | 2                        |

## Salt spray test

|               |   |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h  |

## Mounting

# SK U YE:UNGESTANZT - Marker sheet



0800132

<https://www.phoenixcontact.com/us/products/0800132>

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

0800132

<https://www.phoenixcontact.com/us/products/0800132>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

0800132

<https://www.phoenixcontact.com/us/products/0800132>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)