

# SK U SR:UNGESTANZT - Marker sheet




0800145

<https://www.phoenixcontact.com/us/products/0800145>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker sheet, Din A4, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, Number of individual labels: 1, text field height: 296 mm, text field width: 210 mm



## Your advantages

- The unperforated SK-U... sheets are available for custom label designs
- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements
- Can be printed on all commercially available laser printers
- These labels have been specially developed for laser printers

## Commercial data

Item number	0800145
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	NULL
Product key	BG2114
GTIN	4017918005757
Weight per piece (including packing)	14.69 g
Weight per piece (excluding packing)	14.69 g
Customs tariff number	39199080
Country of origin	FR

## Technical data

### Notes

General	Print image may vary depending on laser printer
---------	---

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	1
Identification technology	Office laser printing

### Dimensions

Width	210.00 mm
Height	297.00 mm
Depth	0.32 mm

### Text field

Text field width	210 mm
Text field height	296 mm

### Material specifications

Foil strength	50 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	silver-colored
Base element material	Polyester

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 120 °C
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	40 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

#### Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
---------------	-------------------------------------

Result	Test passed
--------	-------------

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

#### Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed

#### Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

#### Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

#### Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

#### Mounting

# SK U SR:UNGESTANZT - Marker sheet



0800145

<https://www.phoenixcontact.com/us/products/0800145>

Mounting type	adhesive
---------------	----------

# SK U SR:UNGESTANZT - Marker sheet



0800145

<https://www.phoenixcontact.com/us/products/0800145>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# SK U SR:UNGESTANZT - Marker sheet



0800145

<https://www.phoenixcontact.com/us/products/0800145>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)