

# EMLS (26,5X12)R SR - Safety label with special adhesive



0800353

<https://www.phoenixcontact.com/us/products/0800353>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety label with special adhesive, Roll, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 1000, text field height: 12 mm, text field width: 26.5 mm

## Your advantages

- The EMLS is a tamper-proof label that can be used as a rating plate or a sealing label
- When detaching, a part of the metallized layer separates. It leaves a triangular pattern on the label and substrate. The safety function is reliable up to 80°C
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Labeling service: Phoenix Contact can custom-label all EMLS ... markers according to your requirements
- The EMLS ... materials are UL-listed

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0800353       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG16          |
| Product key                          | BG2411        |
| GTIN                                 | 4046356580403 |
| Weight per piece (including packing) | 143 g         |
| Weight per piece (excluding packing) | 143 g         |
| Customs tariff number                | 39199080      |
| Country of origin                    | PL            |

# EMLS (26,5X12)R SR - Safety label with special adhesive



0800353

<https://www.phoenixcontact.com/us/products/0800353>

## Technical data

### Product properties

|                  |               |
|------------------|---------------|
| Product type     | Device marker |
| Product property | tamper-proof  |

### Marking

|                                     |                  |
|-------------------------------------|------------------|
| Number of individual labels         | 1000             |
| Number of individual labels per row | 3                |
| Identification technology           | Thermal transfer |

### Dimensions

|        |          |
|--------|----------|
| Width  | 26.50 mm |
| Height | 12.00 mm |
| Depth  | 0.06 mm  |

### Text field

|                   |         |
|-------------------|---------|
| Text field width  | 26.5 mm |
| Text field height | 12 mm   |

### Material specifications

|                       |                                |
|-----------------------|--------------------------------|
| Color                 | silver-colored                 |
| Base element material | Polyester                      |
| Components            | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|                                                     |                                                                                          |
|-----------------------------------------------------|------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 150 °C (Functionality of the "triangle symbol" up to approx. +80°C )          |
| Recommended ambient temperature (storage/transport) | 10 °C                                                                                    |
| Recommended humidity (storage/transport)            | 35 % ... 65 % (Storage in a dry and dark place in the original packaging is recommended) |

#### Test for substances that would hinder coating with paint or varnish

|                                                                   |                      |
|-------------------------------------------------------------------|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result                                                            | Test passed          |

#### Test for substances that would hinder coating with paint or varnish

|                                                                   |                    |
|-------------------------------------------------------------------|--------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364:2018-05 |
| Result                                                            | Test passed        |

#### Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

# EMLS (26,5X12)R SR - Safety label with special adhesive



0800353

<https://www.phoenixcontact.com/us/products/0800353>

## Tesafilm test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 125 °C (150 °C) | Test passed                     |

## Wipe resistance of inscriptions

|                                                   |                                                                                        |
|---------------------------------------------------|----------------------------------------------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                       | Test passed                                                                            |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed                                                                            |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                                                            |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                                                            |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                                                            |

## Immersion in chemicals, oil & fuel

|                                               |                          |
|-----------------------------------------------|--------------------------|
| Specification                                 | ISO 175:2010 (following) |
| Test duration                                 | 168 h                    |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ] | Test passed              |
| Ethanol (99 %)<br>[CAS No. 64-17-5]           | Test passed              |
| IRM 901                                       | Test passed              |
| IRM 902                                       | Test passed              |
| IRM 903                                       | Test passed              |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                          |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result        | Test passed              |
| Procedure     | Method B                 |
| Cycles        | 2                        |

## Salt spray test

|               |                                               |
|---------------|-----------------------------------------------|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |

# EMLS (26,5X12)R SR - Safety label with special adhesive



0800353

<https://www.phoenixcontact.com/us/products/0800353>

|               |      |
|---------------|------|
| Test duration | 96 h |
|---------------|------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# EMLS (26,5X12)R SR - Safety label with special adhesive



0800353

<https://www.phoenixcontact.com/us/products/0800353>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0800353>



**cULus Recognized**  
Approval ID: MH48542

# EMLS (26,5X12)R SR - Safety label with special adhesive



0800353

<https://www.phoenixcontact.com/us/products/0800353>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# EMLS (26,5X12)R SR - Safety label with special adhesive



0800353

<https://www.phoenixcontact.com/us/products/0800353>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)