WMS 2,4 (15X4)RXL - Shrink sleeve

0800396

https://www.phoenixcontact.com/us/products/0800396

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLLMASTER 300/600, THERMOMARK ROLL X1, THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK W, THERMOMARK X1.2, cable diameter range: 0.8 ... 2.4 mm, perforated, mounting type: slide-on, Number of individual labels: 10000, text field height: 4 mm, text field width: 15 mm

Product description

Due to their ladder-style format, the preassembled shrink sleeves in the WMS... product family provide a good overview and facilitate quick use. After the printing and applying process, you have the option of shrinking the marked shrink sleeves by applying heat manually and thus fixing them on the cable/wire.

Your advantages

- Permanent and captive identification of single-core wires, wires, cables, pneumatic hoses, and other cylindrical objects
- Ladder style design: For a good overview and to facilitate quick use, the sleeves are preassembled in cut lengths: 15 mm, 30 mm, or 60 mm
- As an option, the sleeves can be shrunk by applying heat manually to fix the sleeve in position
- High diameter coverage with a shrink ratio of 3:1
- Widely used and proven worldwide in control cabinet and machine building, the oil and gas industry, and the railway industry

Commercial data

Item number	0800396
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG14
Product key	BG2216
GTIN	4046356626637
Weight per piece (including packing)	1,146.2 g
Weight per piece (excluding packing)	1,039.3 g
Customs tariff number	39173200
Country of origin	CN

Technical data

Notes

Note on application	For the THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK ROLLMASTER 300/600, and THERMOMARK E.300 (D)/E.600 (D) roll printers, this material can only be processed outside of the printer using the integrated material dispenser pack.
Material information	The specified minimum wire diameter of the shrink sleeve refers to its use as a marking material and does not guarantee any insulation characteristics once shrunk. Depending on the processed material batch, as well as the storage and processing conditions, the maximum insertable wire diameter may be reduced.

Product properties

Product type	Shrink sleeve

Marking

Number of individual labels	10000
Number of individual labels per row	4
Identification technology	Thermal transfer

Dimensions

Width	15 mm
Height	4.9 mm

Text field

Text field width	15 mm
Text field height	4 mm

Material specifications

Color	white (RAL 9010)
Material	Polyolefine
Base element material	polyolefine
Shrink rate	3:1
Components	halogen-free
Shrink temperature	> 85 °C

Cable/line

External cable diameter	0.8 mm ... 2.4 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
Recommended ambient temperature (storage/transport)	23 °C

Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)

Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Methylethylketone (MEK) [CAS No. 78-93-3]	Test passed
Gasoline [CAS No. 64742-49-0]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type	slide-on

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/0800396

CSA
Approval ID: 252259

cULus Recognized
Approval ID: E310982_Vol2_Sec1

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530

UNSPSC

UNSPSC 21.0	39131500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com