

WMS 4,8 (30X9)R CUS - Shrink sleeve

0800748

<https://www.phoenixcontact.com/us/products/0800748>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, white (RAL 9010), cable diameter range: 1.6 ... 4.8 mm: user-defined, perforated or cut, mounting type: slide-on, Number of individual labels: 2, text field height: 9 mm, text field width: 30 mm

Your advantages

- The hoses are preassembled for optimal use of the material
- The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- The sleeves remain flexible after shrinking

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0800748 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8126 |
| GTIN | 4046356628815 |
| Weight per piece (including packing) | 0.58 g |
| Weight per piece (excluding packing) | 0.58 g |
| Country of origin | PL |

WMS 4,8 (30X9)R CUS - Shrink sleeve



0800748

<https://www.phoenixcontact.com/us/products/0800748>

Technical data

Notes

| | |
|----------------------|---|
| Material information | <p>The specified minimum wire diameter of the shrink sleeve refers to its use as a marking material and does not guarantee any insulation characteristics once shrunk.</p> <p>Depending on the processed material batch, as well as the storage and processing conditions, the maximum insertable wire diameter may be reduced.</p> |
|----------------------|---|

Product properties

| | |
|--------------|---------------|
| Product type | Shrink sleeve |
|--------------|---------------|

Marking

| | |
|-------------------------------------|----------------|
| Number of individual labels | 2 |
| Number of individual labels per row | 2 |
| Printing | user-defined |
| Slot type | Shrink sleeve |
| Identification technology | Thermotransfer |

Dimensions

| | |
|--------|-------|
| Width | 9 mm |
| Length | 30 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 30 mm |
| Text field height | 9 mm |

Material specifications

| | |
|-----------------------|------------------|
| Color | white (RAL 9010) |
| Material | Polyolefine |
| Base element material | polyolefine |
| Shrink rate | 3:1 |
| Components | halogen-free |
| Shrink temperature | > 85 °C |

Cable/line

| | |
|-------------------------|-------------------|
| External cable diameter | 1.6 mm ... 4.8 mm |
|-------------------------|-------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -55 °C ... 125 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

WMS 4,8 (30X9)R CUS - Shrink sleeve



0800748

<https://www.phoenixcontact.com/us/products/0800748>

Test for substances that would hinder coating with paint or varnish

| | |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result | Test passed |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 125 °C (150 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |
| Acetone (99 %) [CAS No. 67-64-1] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---------------|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |

WMS 4,8 (30X9)R CUS - Shrink sleeve



0800748

<https://www.phoenixcontact.com/us/products/0800748>

| | |
|---|-------------|
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |
| Acetone (99 %) [CAS No. 67-64-1] | Test passed |
| Methylethylketone (MEK) [CAS No. 78-93-3] | Test passed |
| Gasoline [CAS No. 64742-49-0] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

WMS 4,8 (30X9)R CUS - Shrink sleeve



0800748

<https://www.phoenixcontact.com/us/products/0800748>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0800748>



CSA

Approval ID: 252259



cULus Recognized

Approval ID: E310982_Vol2_Sec1

WMS 4,8 (30X9)R CUS - Shrink sleeve



0800748

<https://www.phoenixcontact.com/us/products/0800748>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

WMS 4,8 (30X9)R CUS - Shrink sleeve



0800748

<https://www.phoenixcontact.com/us/products/0800748>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com