

WMS 2,4 (60X4)R YE CUS - Shrink sleeve




0800755

<https://www.phoenixcontact.com/us/products/0800755>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Shrink sleeve, Roll, yellow (RAL 1018), cable diameter range: 0.8 ... 2.4 mm: user-defined, perforated, mounting type: slide-on



Your advantages

- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- UL 224 (125°C, 600 V, all tubing)
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)

Commercial data

Item number	0800755
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8126
GTIN	4046356628877
Weight per piece (including packing)	0.623 g
Weight per piece (excluding packing)	0.564 g
Country of origin	PL

WMS 2,4 (60X4)R YE CUS - Shrink sleeve



0800755

<https://www.phoenixcontact.com/us/products/0800755>

Technical data

Product properties

Product type	Shrink sleeve
--------------	---------------

Marking

Number of individual labels per row	1
Printing	user-defined
Identification technology	Thermotransfer

Dimensions

Width	4 mm
Length	60 mm

Material specifications

RoHS compliant	yes
Color	yellow (RAL 1018)
Material	Polyolefine
Base element material	polyolefine
Shrink rate	3:1
Components	halogen-free
Shrink temperature	> 85 °C

Cable/line

External cable diameter	0.8 mm ... 2.4 mm
-------------------------	-------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

WMS 2,4 (60X4)R YE CUS - Shrink sleeve



0800755

<https://www.phoenixcontact.com/us/products/0800755>

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Methylethylketone (MEK) [CAS No. 78-93-3]	Test passed
Gasoline [CAS No. 64742-49-0]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
---------------	---------------------------

WMS 2,4 (60X4)R YE CUS - Shrink sleeve



0800755

<https://www.phoenixcontact.com/us/products/0800755>

Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

WMS 2,4 (60X4)R YE CUS - Shrink sleeve



0800755

<https://www.phoenixcontact.com/us/products/0800755>

Classifications

ECLASS

ECLASS-13.0

27281102

ETIM

ETIM 9.0

EC001530

UNSPSC

UNSPSC 21.0

39131500

WMS 2,4 (60X4)R YE CUS - Shrink sleeve



0800755

<https://www.phoenixcontact.com/us/products/0800755>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com