


# UCT-EM (10X8) TQ - Snap-in markers



0801486

<https://www.phoenixcontact.com/us/products/0801486>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Snap-in markers, Sheet, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: latching, Number of individual labels: 36

## Commercial data

Item number	0801486
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG10
Product key	BG2418
GTIN	4046356673365
Weight per piece (including packing)	12.96 g
Weight per piece (excluding packing)	11 g
Customs tariff number	39269097
Country of origin	PL

# UCT-EM (10X8) TQ - Snap-in markers



0801486

<https://www.phoenixcontact.com/us/products/0801486>

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	36
Number of individual labels per row	6

### Dimensions

Width	9.85 mm
Height	7.85 mm
Depth	3.25 mm
Length	8 mm

### Material specifications

RoHS compliant	yes
Color	turquoise
Flammability rating according to UL 94	V0
Base element material	PC
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed

# UCT-EM (10X8) TQ - Snap-in markers



0801486

<https://www.phoenixcontact.com/us/products/0801486>

n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	latching
---------------	----------

# UCT-EM (10X8) TQ - Snap-in markers



0801486

<https://www.phoenixcontact.com/us/products/0801486>

## Classifications

### UNSPSC

UNSPSC 21.0	39131504
-------------	----------

# UCT-EM (10X8) TQ - Snap-in markers



0801486

<https://www.phoenixcontact.com/us/products/0801486>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)