

UCT-EM (10X7) TQ - Snap-in markers



0801499

<https://www.phoenixcontact.com/us/products/0801499>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Snap-in markers, Sheet, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: latching, Number of individual labels: 36

Commercial data

Item number	0801499
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	BG10
Product key	BG2418
GTIN	4046356673471
Weight per piece (including packing)	9.74 g
Weight per piece (excluding packing)	9.5 g
Customs tariff number	39269097
Country of origin	PL

UCT-EM (10X7) TQ - Snap-in markers



0801499

<https://www.phoenixcontact.com/us/products/0801499>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	36
Number of individual labels per row	6

Dimensions

Width	9.99 mm
Height	7.50 mm
Depth	1.00 mm
Length	7 mm

Material specifications

RoHS compliant	yes
Color	turquoise
Flammability rating according to UL 94	V0
Base element material	PC
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed

UCT-EM (10X7) TQ - Snap-in markers



0801499

<https://www.phoenixcontact.com/us/products/0801499>

n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

UCT-EM (10X7) TQ - Snap-in markers



0801499

<https://www.phoenixcontact.com/us/products/0801499>

Classifications

UNSPSC

UNSPSC 21.0	39131504
-------------	----------

UCT-EM (10X7) TQ - Snap-in markers



0801499

<https://www.phoenixcontact.com/us/products/0801499>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com