

UCT-EM (12X3,3) - Snap-in markers



0801502

<https://www.phoenixcontact.com/us/products/0801502>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Snap-in markers, Sheet, white (RAL 9010), unmarked, can be labeled with: BLUEMARK E. CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, Number of individual labels: 30, text field height: 3.3 mm, text field width: 12 mm

Your advantages

- The UCT-EM ... UniCard marking range includes markers for devices and switching devices from a wide range of manufacturers
- The markers, which are supplied in uniform sheets, can be marked quickly, easily, and precisely using the card printers
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	0801502
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG10
Product key	BG2418
GTIN	4046356673495
Weight per piece (including packing)	12 g
Weight per piece (excluding packing)	10.78 g
Customs tariff number	39269097
Country of origin	PL

UCT-EM (12X3,3) - Snap-in markers



0801502

<https://www.phoenixcontact.com/us/products/0801502>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	30
Number of individual labels per row	5
Identification technology	Thermotransfer, UV-LED-Technologie, Laserdirektbeschriftung

Dimensions

Width	11.90 mm
Height	3.30 mm
Depth	4.65 mm

Text field

Text field width	12 mm
Text field height	3.3 mm

Material specifications

Color	white (RAL 9010)
Flammability rating according to UL 94	V0
Base element material	PC
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
---------------	--------------------------------

UCT-EM (12X3,3) - Snap-in markers



0801502

<https://www.phoenixcontact.com/us/products/0801502>

Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	latching
---------------	----------

UCT-EM (12X3,3) - Snap-in markers



0801502

<https://www.phoenixcontact.com/us/products/0801502>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT-EM (12X3,3) - Snap-in markers



0801502

<https://www.phoenixcontact.com/us/products/0801502>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.047 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com