


# CES-STPG-GY-2ASI-LR - Cable sleeve



0801714

<https://www.phoenixcontact.com/us/products/0801714>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable sleeve, small, no. of conductors: 2, type: AS-i cable (Left Right), slotted, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

## Product description

Slotted sleeves for accommodating two preassembled AS-i cables (LL), can be used in CES sealing frames. When fitted, the sleeves also ensure strain relief in accordance with DIN EN 50262

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0801714       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF67          |
| Product key                          | AF7CCX        |
| GTIN                                 | 4046356675154 |
| Weight per piece (including packing) | 7.12 g        |
| Weight per piece (excluding packing) | 7.12 g        |
| Customs tariff number                | 40169997      |
| Country of origin                    | PL            |

0801714


<https://www.phoenixcontact.com/us/products/0801714>

## Technical data

### Product properties

|                   |              |
|-------------------|--------------|
| Product type      | Cable sleeve |
| No. of conductors | 2            |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 19.5 mm  |
| Height              | 17 mm  |
| Length              | 29.5 mm  |

### Material specifications

|  |                     |
|--|---------------------|
| Material                               | SEBS (halogen-free) |
| Flammability rating according to UL 94 | V0                  |

### Characteristics

|                         |            |
|-------------------------|------------|
| Conductor sealing range | AS-i cable |
| Seal size               | small      |
| Design, Format          | AS-i cable |
| Design, Cable seal      | slotted    |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                           |
|---------------------------------|---------------------------|
| Degree of protection            | IP54                      |
| Ambient temperature (operation) | -40 °C ... 80 °C (static) |

# CES-STPG-GY-2ASI-LR - Cable sleeve




0801714

<https://www.phoenixcontact.com/us/products/0801714>

## Drawings

Dimensional drawing



Dimensional drawing

# CES-STPG-GY-2ASI-LR - Cable sleeve



0801714

<https://www.phoenixcontact.com/us/products/0801714>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0801714>



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026

**DNV**

Approval ID: TAE00003VJ

# CES-STPG-GY-2ASI-LR - Cable sleeve



0801714

<https://www.phoenixcontact.com/us/products/0801714>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27144425 |
| ECLASS-15.0 | 27144425 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000451 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CES-STPG-GY-2ASI-LR - Cable sleeve



0801714

<https://www.phoenixcontact.com/us/products/0801714>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.057 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)