

TML (EX5)R - Marker strip

0801838

<https://www.phoenixcontact.com/us/products/0801838>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker strip, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 10, roll length: 30 m, text field height: 5 mm, text field width: 30000 mm

Your advantages

- The self-adhesive marker strips from the SK marking range mark products without a marker groove, ideal for marking COMBICON connectors
- Zack marker strips and flat zack marker strips can be marked subsequently with the TML marking foil
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The thermal transfer printer cutting units make it possible to trim precisely to the required length
- Labeling service: Phoenix Contact can custom-label all TML ... markers in accordance with your requirements

Commercial data

Item number	0801838
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG11
Product key	BG2111
GTIN	4046356750585
Weight per piece (including packing)	444.421 g
Weight per piece (excluding packing)	444.421 g
Customs tariff number	39199080
Country of origin	PL

Technical data

Product properties

Product type	Terminal marker
--------------	-----------------

Marking

Number of individual labels	10
Number of individual labels per row	1
Number of marker strips	10
Slot type	flat
Identification technology	Thermal transfer

Dimensions

Length of roll	30.00 m
Height	5.00 mm
Depth	0.07 mm

Text field

Text field width	30000 mm
Text field height	5 mm

Material specifications

RoHS compliant	yes
Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed

TML (EX5)R - Marker strip



0801838

<https://www.phoenixcontact.com/us/products/0801838>

Test duration	96 h
---------------	------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

TML (EX5)R - Marker strip

0801838

<https://www.phoenixcontact.com/us/products/0801838>



Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

TML (EX5)R - Marker strip



0801838

<https://www.phoenixcontact.com/us/products/0801838>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com