

# US-EMP (25X6)-1 CUS - Snap-in markers



0802755

<https://www.phoenixcontact.com/us/products/0802755>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Snap-in markers, Card, can be ordered: by card, white (RAL 9010), labeled according to customer specifications, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, Number of individual labels: 84, text field height: 6 mm, text field width: 25 mm

## Your advantages

- All US-EMP ... device markers can also be supplied labeled according to customer requirements
- The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts

## Commercial data

Item number	0802755
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
GTIN	4046356858472
Weight per piece (including packing)	10 g
Weight per piece (excluding packing)	10 g
Country of origin	PL

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	84
Number of individual labels per row	4
Identification technology	Thermotransfer

### Dimensions

Width	25.00 mm
Height	6.10 mm
Depth	0.30 mm
Length	6 mm

### Text field

Text field width	25 mm
Text field height	6 mm

### Material specifications

Color	white (RAL 9010)
Material	PVC
	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

# US-EMP (25X6)-1 CUS - Snap-in markers



0802755

<https://www.phoenixcontact.com/us/products/0802755>

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	snapped into marker carrier
---------------	-----------------------------

# US-EMP (25X6)-1 CUS - Snap-in markers



0802755

<https://www.phoenixcontact.com/us/products/0802755>

## Classifications

### ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131700
-------------	----------

# US-EMP (25X6)-1 CUS - Snap-in markers



0802755

<https://www.phoenixcontact.com/us/products/0802755>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)