

# UCT-PMP (90X38) CUS - Insert label



0803040

<https://www.phoenixcontact.com/us/products/0803040>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert label, Sheet, white (RAL 9010), labeled according to customer specifications, mounting type: snapped into marker carrier, Number of individual labels: 1, text field height: 38 mm, text field width: 90 mm



## Your advantages

- The UCT-PMP (90x38) system marking label is easy to mount and, if necessary, remove
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- Marking service: Phoenix Contact can custom-mark all labels according to your requirements

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0803040                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8148                         |
| GTIN                                 | 4046356908078                  |
| Weight per piece (including packing) | 9.8 g                          |
| Weight per piece (excluding packing) | 9.8 g                          |
| Country of origin                    | PL                             |

# UCT-PMP (90X38) CUS - Insert label



0803040

<https://www.phoenixcontact.com/us/products/0803040>

## Technical data

### Product properties

|              |              |
|--------------|--------------|
| Product type | Plant marker |
|--------------|--------------|

### Marking

|                                     |   |
|-------------------------------------|---|
| Number of individual labels         | 1                                       |
| Number of individual labels per row | 1                                       |
| Identification technology           | UV LED technology, direct laser marking |

### Dimensions

|        |          |
|--------|----------|
| Width  | 90.00 mm |
| Height | 38.00 mm |
| Depth  | 1.15 mm  |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 90 mm |
| Text field height | 38 mm |

### Material specifications

|  |                                |
|--|--------------------------------|
| Color  | white (RAL 9010)               |
| Flammability rating according to UL 94                 | V0                             |
| Base element material                                  | PC                             |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3                    |
| Components   | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -40 °C ... 100 °C   |
| Recommended ambient temperature (storage/transport) | 23 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### Test for substances that would hinder coating with paint or varnish

|   |                         |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result  | Test passed             |

#### Test for substances that would hinder coating with paint or varnish

|   |                      |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result  | Test passed          |

#### Scratch resistance

# UCT-PMP (90X38) CUS - Insert label



0803040

<https://www.phoenixcontact.com/us/products/0803040>

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

## Tesa film test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 100 °C (121 °C) | Test passed                     |

## Wipe resistance of inscriptions

|   |  |
|---|--|
| Specification                                   | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                     | Test passed  |
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed  |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed  |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                      |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result        | Test passed          |
| Procedure     | Method B             |
| Cycles        | 2                    |

## Salt spray test

|               |   |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h  |

## Standards and regulations

### Standards

|                       |            |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

## Mounting

|               |                             |
|---------------|-----------------------------|
| Mounting type | snapped into marker carrier |
|---------------|-----------------------------|

# UCT-PMP (90X38) CUS - Insert label



0803040

<https://www.phoenixcontact.com/us/products/0803040>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281104 |
| ECLASS-15.0 | 27281104 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# UCT-PMP (90X38) CUS - Insert label



0803040

<https://www.phoenixcontact.com/us/products/0803040>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.053 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)