


UCT-PMP (90X38) BU - Insert label

0803047

<https://www.phoenixcontact.com/us/products/0803047>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert label, Sheet, blue (RAL 5015), unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, TOPMARK NEO, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, Number of individual labels: 1, text field height: 38 mm, text field width: 90 mm

Your advantages

- The UCT-PMP (90x38) system marking label is easy to mount and, if necessary, remove
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- The markers, which are supplied in uniform sheets, can be marked quickly and easily using the BLUEMARK ID..., BLUEMARK CLED, TOPMARK LASER, or TOPMARK NEO
- The format automatically ensures printing with a high degree of positioning accuracy
- Marking service: Phoenix Contact can custom-mark all labels according to your requirements

Commercial data

Item number	0803047
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG2617
GTIN	4046356933506
Weight per piece (including packing)	10.58 g
Weight per piece (excluding packing)	10.5 g
Country of origin	PL

UCT-PMP (90X38) BU - Insert label



0803047

<https://www.phoenixcontact.com/us/products/0803047>

Technical data

Product properties

Product type	Plant marker
--------------	--------------

Marking

Number of individual labels	1
Number of individual labels per row	1
Identification technology	UV LED technology, direct laser marking

Dimensions

Width	90.00 mm
Height	38.00 mm
Depth	1.15 mm

Text field

Text field width	90 mm
Text field height	38 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
Base element material	PC
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

UCT-PMP (90X38) BU - Insert label



0803047

<https://www.phoenixcontact.com/us/products/0803047>

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

UCT-PMP (90X38) BU - Insert label



0803047

<https://www.phoenixcontact.com/us/products/0803047>

Test duration	96 h
---------------	------

Standards and regulations

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	snapped into marker carrier
---------------	-----------------------------

UCT-PMP (90X38) BU - Insert label



0803047

<https://www.phoenixcontact.com/us/products/0803047>

Classifications

ECLASS

ECLASS-13.0	27281104
ECLASS-15.0	27281104

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT-PMP (90X38) BU - Insert label



0803047

<https://www.phoenixcontact.com/us/products/0803047>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.003 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com