

WML-RFID/HF 14 (25X19)R - Cable marker



0803386

<https://www.phoenixcontact.com/us/products/0803386>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker label with RFID-HF transponder, roll, white, unmarked, can be printed with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X1.2, mounting type: adhesive, min. cable diameter: 9 mm, max. cable diameter: 14 mm, lettering field size: 25 x 19 mm

Your advantages

- High-quality marking created by the thermal transfer printer
- Resistant to solvents
- The cable marker labels consist of a labeling field and a transparent protective foil
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- Quick and easy handling
- The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example

Commercial data

Item number	0803386
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG2311
GTIN	4055626047751
Weight per piece (including packing)	418.5 g
Weight per piece (excluding packing)	368.31 g
Country of origin	DE

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	750
Number of individual labels per row	1
Identification technology	Thermal transfer

Electrical properties

Frequency range	13.56 MHz
-----------------	-----------

Dimensions

Width	25.4 mm
Height	63.5 mm
Depth	0.35 mm

Text field

Text field width	25.4 mm
Text field height	19.1 mm

Material specifications

Color	white (RAL 9010)
Base element material	PVC
Components	Free from silicone and cadmium

Cable/line

External cable diameter	14.20 mm
	6.1 mm ... 14.2 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	40 % ... 50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
---	--------------------

WML-RFID/HF 14 (25X19)R - Cable marker



0803386

<https://www.phoenixcontact.com/us/products/0803386>

Result	Test passed
--------	-------------

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

WML-RFID/HF 14 (25X19)R - Cable marker



0803386

<https://www.phoenixcontact.com/us/products/0803386>

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Mounting

Mounting type	adhesive
---------------	----------

WML-RFID/HF 14 (25X19)R - Cable marker



0803386

<https://www.phoenixcontact.com/us/products/0803386>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0803386>



UL Recognized

Approval ID: MH48542

WML-RFID/HF 14 (25X19)R - Cable marker



0803386

<https://www.phoenixcontact.com/us/products/0803386>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WML-RFID/HF 14 (25X19)R - Cable marker



0803386

<https://www.phoenixcontact.com/us/products/0803386>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com