

# ZBF 6/9,2 S8,LGS:1-8 - Zack marker strip



0803450

<https://www.phoenixcontact.com/us/products/0803450>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white (RAL 9010), labeled, can be labeled with: CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 6.2 mm, Number of individual labels: 8, text field height: 10.5 mm, text field width: 6 mm

## Your advantages

- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- The multi-section marking strips are easy to fit and can be easily separated if required

## Commercial data

Item number	0803450
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4055626072173
Weight per piece (including packing)	0.64 g
Weight per piece (excluding packing)	0.64 g
Customs tariff number	49119900
Country of origin	DE

# ZBF 6/9,2 S8,LGS:1-8 - Zack marker strip



0803450

<https://www.phoenixcontact.com/us/products/0803450>

## Technical data

### Product properties

Product type	Terminal marker
Pitch	6.2 mm

### Marking

Number of individual labels	8
Slot type	flat

### Dimensions

Width	6.40 mm
Height	70.20 mm
Depth	1.60 mm
Pitch	6.2 mm

### Text field

Text field width	6 mm
Text field height	10.5 mm

### Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
---------------	-------------------------------------

# ZBF 6/9,2 S8,LGS:1-8 - Zack marker strip



0803450

<https://www.phoenixcontact.com/us/products/0803450>

Result	Test passed
--------	-------------

## UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	120 °C

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	latching
---------------	----------

# ZBF 6/9,2 S8,LGS:1-8 - Zack marker strip



0803450

<https://www.phoenixcontact.com/us/products/0803450>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# ZBF 6/9,2 S8,LGS:1-8 - Zack marker strip



0803450

<https://www.phoenixcontact.com/us/products/0803450>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.006 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)