

EMT (9,8X38,2)R TQ - Insert label

0803893

<https://www.phoenixcontact.com/us/products/0803893>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert label, for marking Silo and Murrelektronik controllers, Roll, pastel turquoise (6034), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: insert, Number of individual labels: 500, text field height: 9.8 mm, text field width: 38.2 mm

Your advantages

- EMT (9,8x38,2)R TQ, turquoise insert label, for marking Silo and Murrelektronik controllers
- Thanks to their special shape, the EMT (9,8x38,2)R insert labels remain securely inside the collar of the Silo and Murrelektronik controllers once inserted
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Marking service: Phoenix Contact can custom-mark all EMT ... markers according to your requirements

Commercial data

Item number	0803893
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG2411
GTIN	4055626193229
Weight per piece (including packing)	131 g
Weight per piece (excluding packing)	131 g
Country of origin	DE

EMT (9,8X38,2)R TQ - Insert label



0803893

<https://www.phoenixcontact.com/us/products/0803893>

Technical data

Product properties

Product type	Device marker
Area of application	Silo and Murrelektronik controllers
Controller type	for marking Silo and Murrelektronik controllers

Marking

Number of individual labels	500
Number of individual labels per row	1
Identification technology	Thermal transfer

Dimensions

Width	38.20 mm
Height	9.80 mm
Depth	0.18 mm

Text field

Text field width	38.2 mm
Text field height	9.8 mm

Material specifications

Foil strength	175 µm
Color	pastel turquoise (RAL 6034)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

EMT (9,8X38,2)R TQ - Insert label



0803893

<https://www.phoenixcontact.com/us/products/0803893>

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

EMT (9,8X38,2)R TQ - Insert label



0803893

<https://www.phoenixcontact.com/us/products/0803893>

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	insert
---------------	--------

EMT (9,8X38,2)R TQ - Insert label



0803893

<https://www.phoenixcontact.com/us/products/0803893>

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

EMT (9,8X38,2)R TQ - Insert label



0803893

<https://www.phoenixcontact.com/us/products/0803893>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com