

WP-PA HF-HB 34,5 BK 15M - Protective hose



0803901

<https://www.phoenixcontact.com/us/products/0803901>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: PA, UV-resistant: yes, flexible, degree of protection: IP67, color: black, inside diameter: 29 mm

Commercial data

Item number	0803901
Packing unit	1 pc
Minimum order quantity	200 pc
Product key	AF7DSA
GTIN	4055626200866
Weight per piece (including packing)	1,499.85 g
Weight per piece (excluding packing)	1,499.85 g
Country of origin	DE

WP-PA HF-HB 34,5 BK 15M - Protective hose



0803901

<https://www.phoenixcontact.com/us/products/0803901>

Technical data

Notes

Notes on operation	Protective hose length is measured stretched out; length tolerance $\pm 5\%$
Order information:	1 packing unit = 15 m roll

Product properties

Product type	Protective hose
Tensile strength GRP	100 N

Dimensions

External dimensions

Outside diameter	34.5 mm
------------------	---------

Internal dimensions

Internal diameter	29 mm
-------------------	-------

Material specifications

Material	PA
Components	free from silicone, halogen, and cadmium

Cable/line

Bending radius, static	65 mm
Tensile strength	100 N
Halogen-free	yes

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 115 °C
Resistance to UV radiation	yes

WP-PA HF-HB 34,5 BK 15M - Protective hose



0803901

<https://www.phoenixcontact.com/us/products/0803901>

Classifications

ECLASS

ECLASS-13.0

27430304

ETIM

ETIM 9.0

EC001177

UNSPSC

UNSPSC 21.0

40141700

WP-PA HF-HB 34,5 BK 15M - Protective hose



0803901

<https://www.phoenixcontact.com/us/products/0803901>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com