

MM-WML 5 (EX10)R C1 WH/BK - Cable marker label



0803932

<https://www.phoenixcontact.com/us/products/0803932>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker label, Roll, Mixed color, unmarked, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, cable diameter range: 2 ... 5 mm, mounting type: adhesive, cable diameter: ≤ 5 mm, Number of individual labels: 1, text field height: 8 mm, text field width: 6500 mm

Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- Thanks to the continuous format, a wrap-around label of the appropriate width can be created flexibly for the relevant application
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The transparent protective foil is wound over the marking and provides permanent protection against contamination and abrasion
- The wrap-around labels do not add bulk, which means that the cable can still be drawn through cable ducts, for example
- The material is cUL certified



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0803932 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG23 |
| Product key | BG221E |
| GTIN | 4055626212128 |
| Weight per piece (including packing) | 85.2 g |
| Weight per piece (excluding packing) | 82.4 g |
| Customs tariff number | 96121010 |
| Country of origin | CN |

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-------------------------------------|------------------|
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |
| Identification technology | Thermal transfer |

Dimensions

| | |
|--------|-------|
| Height | 24 mm |
| Length | 6.5 m |

Text field

| | |
|-------------------|---------|
| Text field width | 6500 mm |
| Text field height | 8 mm |

Material specifications

| | |
|-----------------------|--------------------------------|
| Foil strength | 89 µm |
| Adhesive strength | 23 µm |
| Adhesive | Acrylic |
| Color | multicolored (RAL -) |
| | white (RAL 9010) |
| | black (RAL 9005) |
| Material | Vinyl polymer |
| Base element material | Vinyl polymer |
| Components | Free from silicone and cadmium |

Cable/line

| | |
|-------------------------|---------------|
| External cable diameter | ≤ 5.00 mm |
| | 2 mm ... 5 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 21 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

0803932

<https://www.phoenixcontact.com/us/products/0803932>

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Wipe resistance of inscriptions

| | |
|---|---|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

MM-WML 5 (EX10)R C1 WH/BK - Cable marker label



0803932

<https://www.phoenixcontact.com/us/products/0803932>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0803932>



cULus Recognized
Approval ID: MH48542

0803932

<https://www.phoenixcontact.com/us/products/0803932>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

0803932

<https://www.phoenixcontact.com/us/products/0803932>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 1.302 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com